CQB100W-110S SERIES
100 WATT 4:1 INPUT ISOLATED DC-DC CONVERTER

Features

- Efficiency Up to 92%
- Fixed Switching Frequency
- Regulated Outputs
- Remote On/Off
- Low No Load Power Consumption
- Fully Protected (OTP/OCP/OVP/UVLO)
- 3000Vdc I/O Isolation
- Operating Case Temperature -40 to +105℃
- Quarter Brick Size Meet Industrial Standard 2.28"x1.45"x0.5"
- CB Test Certificate IEC 60950-1 (Except 15Vout)
- UL 60950-1 2nd (Basic Insulation) Approval (Except 15Vout)
- EN 50155 Compliant with External Circuits
- Shock & Vibration EN 50155 (EN 61373) Compliant
- Fire & Smoke EN 45545-2 Compliant
- 3000m Operating Altitude
- Safety Meets IEC/EN/UL 62368-1



E176177

MODEL NUMBER	INPUT VOLTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT		INPUT CURRENT		% EFF.	CAPACITOR LOAD MAX.
			MIN.	MAX.	NO LOAD	FULL LOAD	(1)	
CQB100W-110S05	43-160 VDC	5 VDC	0 mA	20 A	10 mA	1.00 A	91	20000μF
CQB100W-110S12	43-160 VDC	12 VDC	0 mA	8.4 A	10 mA	1.00 A	92	8400μF
CQB100W-110S15	43-160 VDC	15 VDC	0 mA	6.7 A	10 mA	1.00 A	91	6700μF
CQB100W-110S24	43-160 VDC	24 VDC	0 mA	4.2 A	10 mA	1.03 A	89	4200μF
CQB100W-110S28	43-160 VDC	28 VDC	0 mA	3.6 A	10 mA	1.04 A	88.5	3600μF
CQB100W-110S48	43-160 VDC	48 VDC	0 mA	2.1 A	10 mA	1.02 A	90	1000μF

NOTE:

1. Nominal Input Voltage 110 VDC.
2. An External Input Capacitor 220uF for All Models are Recommended to Reduce Input Ripple Voltage.
3. To Meet EN50155 and RIA12 refer to Application Note.

PART NUMBER

Series	Nominal Input Voltage	Number of Outputs	Nominal Output Voltage	Remote On/Off Logic	Mounting Inserts
CQB100W-	II	O	XX	L	-Y (Option)
CQB100W	110：110 VDC	S：Single	05：05VDC 12：12VDC 15：15VDC 24：24VDC 28：28VDC 48：48VDC	None：Positive N：Negative	None： M3x0.5 Mounting Inserts -C： Clear Mounting Insert (3.2mm DIA.)

Part Number Example:

CQB100W-110S12N-C: Quarter Brick, 100W, 4:1 43-160Vdc Input, Single 12Vdc Output, Negative Logic, Clear Mounting Insert

Downloaded from Arrow.com.

TECHNICAL SPECIFICATIONS

(All specifications are typical at nominal input, full load at 25℃ unless otherwise noted.)

ABSOLUTE MAXIMUM RATINGS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Input Voltage	Continuous	All	-0.3		160	V_{dc}
Input Surge Voltage	100ms	All			200	V_{dc}
Operating Case Temperature		All	-40		105	℃
Storage Temperature		All	-55		125	℃

INPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Operating Input Voltage		All	43	110	160	V_{dc}
Input Under Voltage Lockout						
Turn-On Voltage Threshold		All	40.5	41.5	42.5	V_{dc}
Turn-Off Voltage Threshold		All	37	38	39	V_{dc}
Lockout Hysteresis Voltage		All		3.5		V_{dc}
Maximum Input Current	V_{in}=43V, Full load	All		2.6		A
No-Load Input Current	V_{in}=110V, I_o=0A	All		10		mA
Input Filter	Pi filter	All				
Inrush Current (I^2t)	As per ETS300 132-2.	All			0.1	A^2s
Input Reflected Ripple Current	P-P thru 12uH inductor, 5Hz to 20MHz	All		30		mA

OUTPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Voltage Set Point Accuracy	V_{in}=110V, Full load, T_c=25℃	All	-1.0		+1.0	%
Output Voltage Regulation						
Load Regulation	Full load to no load	All			±0.2	%
Line Regulation	V_{in}=High line to low line, full load	All			±0.2	%
Temperature Coefficient	T_c=-40℃ to 105℃	All			±0.02	%/℃
Output Voltage Ripple and Noise (5Hz to 20MHz bandwidth)						
Peak-to-Peak	Full load, 10uF tantalum and 1uF ceramic capacitors (for V_o=48V: Full load 10uF aluminum and 1uF ceramic capacitors)	5Vo			100	mV
		12Vo			150	
		15Vo			150	
		24Vo			240	
		28Vo			240	
		48Vo			480	
RMS.		5Vo			40	mV
		12Vo			60	
		15Vo			60	
		24Vo			100	
		28Vo			100	
		48Vo			200	
Output Current Range	V_{in}= 43 to 160V	See Model Number Table				A
Over Current Protection	Hiccup mode. Auto recovery	All	110	125	160	%
Over Voltage Protection	Limited voltage, % of nominal V_o	All	115	125	140	%
Short Circuit Protection		All	Continuous			
External Load Capacitance	Full load (resistive)	See Model Number Table				uF

Downloaded from Arrow.com.

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Output Voltage Trim Range	$P_o \leqq$ max. rated power, $I_o \leqq I_{o_max.}$	15Vout Others	-20 -10		+10 +10	%
Output Voltage Remote Sense Range	$P_o \leqq$ max. rated power, $I_o \leqq I_{o_max.}$ % of nominal V_o	All			+10	%

EFFICIENCY

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
100% Load	V_{in}=110V	See Model Number Table				%

DYNAMIC CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Output Voltage Current Transient						
Error Band	75% to 100% of $I_{o_max.}$ step load change d_i/d_t=0.1A/us (within 1% V_{out} nominal)	All			±5	%
Recovery Time					250	us
Turn-On Delay and Rise Time	Full load (constant resistive load)					
Turn-On Delay Time, From On/Off Control	$V_{on/off}$ to 10%V_{o_set}	All		30		ms
Turn-On Delay Time, From Input	$V_{in_min.}$ to 10%V_{o_set}	All		30		ms
Output Voltage Rise Time	10%V_{o_set} to 90%V_{o_set}	All		30		ms

ISOLATION CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Isolation Voltage	1 Minute; input to output 1 Minute; input to case 1 Minute; output to case	All			3000 2250 500	V_{dc} V_{dc} V_{ac}
Isolation Resistance	Input to output	All	100			MΩ
Isolation Capacitance	Input to output Input to case (base plate)	All		1500 None		pF
	Output to case	5Vo 12Vo 15Vo 24Vo 28Vo 48Vo		470 10000 10000 3000 3000 4700		

FEATURE CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Switching Frequency	Pulse width modulation (PWM), fixed	All	270	300	330	KHz
On/Off Control, Positive Remote On/Off Logic, Refer to -Vin Pin						
Logic Low (Module Off)	$V_{on/off}$ at $I_{on/off}$=1.0mA	All	0		1.2	V
Logic High (Module On)	$V_{on/off}$ at $I_{on/off}$=0.0uA	All	3.5 or Open Circuit		160	V
On/Off Control, Negative Remote On/Off Logic, Refer to -Vin Pin						
Logic High (Module Off)	$V_{on/off}$ at $I_{on/off}$=0.0uA	All	3.5 or Open Circuit		160	V
Logic Low (Module On)	$V_{on/off}$ at $I_{on/off}$=1.0mA	All	0		1.2	V
On/Off Current (for Both Remote On/Off Logic)	$I_{on/off}$ at $V_{on/off}$=0V	All		0.3	1	mA
Leakage Current (for Both Remote On/Off Logic)	Logic high, $V_{on/off}$=15V	All			30	uA
Off Converter Input Current	Shutdown input idle current	All		5	10	mA
Over Temperature Shutdown	Temperature at the center part of base plate, non-latching	All		110		℃
Over Temperature Recovery				100		

Downloaded from Arrow.com.

GENERAL SPECIFICATIONS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
MTBF	I_o=100% of $I_{o_max.}$; MIL-HDBK - 217F_Notice 1, GB, 25℃	5Vo 12Vo Others		720 720 840		K hours
Weight		All		68		grams
Case Material	Plastic, DAP					
Base plate Material	Aluminum					
Potting Material	UL 94V-0					
Pin Material	Base: Copper Plating: Nickel with Matte Tin					
Shock/Vibration	MIL-STD-810F/EN 61373 Compliant					
Humidity	95% RH max. Non condensing					
Altitude	3000m Operating altitude, 12000m Transport altitude					
Thermal Shock	MIL-STD-810F					
Fire & Smoke	EN 45545-2 Compliant					

EMC SPECIFICATIONS (External components required, please refer to application note.)

EMI	Meets EN 55011, EN 55032 & EN 50155 Compliant (with external filter)		Class A
ESD	EN 61000-4-2	Level 3: Air ±8kV, Contact ±6kV	Perf. Criteria A
Radiated immunity	EN 61000-4-3	Level 3: 80~1000MHz, 20V/m Level 2: 80~1000MHz, 3V/m for EN 55035:2017	Perf. Criteria A
Fast Transient	EN 61000-4-4	Level 3: On power input port, ±2kV, external input capacitor required Level 1: On power input port, ±0.5kV, external input capacitor required, for EN55035:2017	Perf. Criteria A
Surge	EN 61000-4-5	Level 4: Line to earth, ±4kV, Line to line, ±2kV (EN 50155) Level 1: Line to earth, ±0.5kV, for EN 55035:2017 external components required	Perf. Criteria A
Conducted immunity	EN 61000-4-6	Level 3: 0.15~80MHz, 10V Level 2: 0.15~30MHz, 3V, 30~80MHz, 1V for EN 55035:2017	Perf. Criteria A
Magnetic Immunity	EN 61000-4-8	Level 1: 50Hz, 1A/m for EN 55035:2017	Perf. Criteria A
Interruptions of Voltage Supply	EN 50155	Class S2: 10ms interruptions	Perf. Criteria B
Supply Change Over	EN 50155	Class C2: During a supply break of 30 ms	Perf. Criteria B
Application Note Link			CQB100W-110S Series App Notes
Packaging Information Link			Packaging Information

Downloaded from Arrow.com.

Immunity to Environmental Conditions

Phenomenon	EN 50155; 2017 Reference Clause(s)	Reference Standard	Test Conditions	Result
Low Temperature Start-up test	13.4.4	EN 60068-2-1	Class OT6 Temperature: -40℃ Duration: 2 hrs	Pass
Dry Heat Test	13.4.5	EN 60068-2-2	Class OT6 & ST2 Temperature: 85℃ Duration: 6 hrs Extended temperature: 100℃ Extended Duration: 10min	Pass
Low Temperature Storage Test	13.4.6	EN 60068-2-1	Temperature: -40℃ Duration: 16 hrs	Pass
Cyclic Damp Heat Test	13.4.7	EN 60068-2-30	Temperature: 25℃ - 55℃ Humidity: 90% RH Duration: 48 hrs	Pass
Random Vibration Test	13.4.11	EN 61373	Temperature: 25℃±10℃ Humidity: 50% ±25% RH Frequency range: 5 ~ 150 Hz Vertical: 1.01 m/s^2 Transverse: 0.450 m/s^2 Longitudinal: 0.700 m/s^2 Duration: 10 min / axis	Pass
Simulated Long Life Test at Increased Random Vibration Levels	13.4.11	EN 61373	Temperature: 25℃±10℃ Humidity: 50% ±25% RH Frequency range: 5 ~ 150 Hz Vertical: 5.72 m/s^2 Transverse: 2.55 m/s^2 Longitudinal: 3.96 m/s^2 Duration: 5 hrs / axis	Pass
Shock Test	13.4.11	EN 61373	Temperature: 25℃±10℃ Humidity: 50% ±25% RH Frequency range: 5 ~ 150 Hz ±Vertical: 30 m/s^2 ±-Transverse: 30 m/s^2 ±Longitudinal: 50 m/s^2 Duration: 30ms x18 (Each axis 3 shocks)	Pass

EN 45545-2 Fire & Smoke Test Conditions


Item		Standard	Hazard Level
R22	Oxygen Index Test	EN 45545-2: 2013+A1:2015 EN ISO 4589-2: 2017	HL1, HL2, HL3
	Smoke Density Test	EN 45545-2: 2013+A1:2015 EN ISO 5659-2: 2017	HL1, HL2, HL3
	Smoke Toxicity Test	EN 45545-2: 2013+A1:2015 NF X70-100-1 and -2: 2006	HL1, HL2, HL3
R23	Oxygen Index Test	EN 45545-2: 2013+A1:2015 EN ISO 4589-2: 2017	HL1, HL2, HL3
	Smoke Density Test	EN 45545-2: 2013+A1:2015 EN ISO 5659-2: 2013	HL1, HL2, HL3
	Smoke Toxicity Test	EN 45545-2: 2013+A1:2015 NF X70-100-1 and -2: 2006	HL1, HL2, HL3
R24	Oxygen Index Test	EN 45545-2: 2013 EN ISO 4589-2	HL1, HL2, HL3
R25	Glow - Wire Test	EN 45545-2+A1:2016 EN 60695-2-11:2014	HL1, HL2, HL3
R26	Vertical Flame Test	EN 45545-2: 2013 EN 60695-11-10: 2013	HL1, HL2, HL3

Downloaded from Arrow.com.


CHARACTERISTIC CURVE

Power Derating Curve


CQB100W-110S05,12,15 Derating Curve without Heatsink (Vin=110V)




CQB100W-110S24,28 Derating Curve without Heatsink (Vin=110V)




CQB100W-110S48 Derating Curve without Heatsink (Vin=110V)




CQB100W-110S05,12,15 Derating Curve with Heatsink QBL127 (Vin=110V))




CQB100W-110S24,28 Derating Curve with Heatsink QBL127 (Vin=110V))




CQB100W-110S48 Derating Curve with Heatsink QBL127 (Vin=110V))




CQB100W-110S05,12,15 Derating Curve with Heatsink QBT210 (Vin=110V))




CQB100W-110S24,28 Derating Curve with Heatsink QBT210 (Vin=110V))





Downloaded from Arrow.com.





Performance Data
















Downloaded from Arrow.com.


CQB100W-110S24
Eff Vs Io @25 Deg. C




CQB100W-110S24
Pd Vs Po @25 Deg. C




CQB100W-110S28
Eff Vs Io @25 Deg. C




CQB100W-110S28
Pd Vs Po @25 Deg. C



CQB100W-110S48
Eff Vs Io @25 Deg. C




CQB100W-110S48
Pd Vs Po @25 Deg. C



Downloaded from Arrow.com.

MECHANICAL SPECIFICATION



All Dimensions in Inches[mm]
Tolerance Inches: x.xx=±0.02, x.xxx=±0.010
Millimeters: x.x=±0.5, x.xx=±0.25

Pin Connection

Pin	Function
1	+V Input
2	On/Off
3	-V Input
4	-V Output
5	-Sense
6	Trim
7	+Sense
8	+V Output

Note:Pin Size is ∅0.04±0.004 Inch [∅1.0±0.1 mm]
Pin Size is ∅0.06±0.004 Inch [∅1.5±0.1 mm]

CINCON Electronics Co. Ltd.
Add: 14F, No. 306, Sec.4, Hsin Yi Rd., Taipei, Taiwan
Tel: 886-2-27086210
Fax: 886-2-27029852
E-mail: sales@cincon.com.tw
Web: www.cincon.com

Downloaded from Arrow.com.