





	1	2	3	4	5	6	7																																																																																							
A	   PCB Layout							A																																																																																						
B								B																																																																																						
C								C																																																																																						
D	 Material: Contact: Phosphor Bronze thickness 0.15mm Plating: Contact Plating,Tin plated 60u"~80u" Insulator: PBT-4830,UL 94V-0 SPECIFICATIONS: Current Rating:1A Dielectric withstanding Voltage:1000v RMS/minute Insulator resistance:5000 Megohms min. Contact resistance:20 milliohms initial 30 milliohms after test. Operating temperatures:-55°C to 85°C Insertion force:340g(12 oz)max.per contact. Withdrawal force:80g(2.82 oz)min.per contact.							D																																																																																						
E								E																																																																																						
F								F																																																																																						
G	RoHS compliant Unit: mm <table><tr><td>Scale</td><td>FREE</td><td></td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td>Customer-No.</td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>29.07.2014</td><td>Amy</td><td></td></tr><tr><td>X.</td><td>±0.38</td><td></td><td></td><td></td><td></td><td>Approved</td><td>17.10.2014</td><td>Amy</td><td></td></tr><tr><td>X.X</td><td>±0.25</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XX</td><td>±0.13</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td>①</td><td>Update P/N to 22 pins version</td><td>17.10.2014</td><td>Ray</td><td colspan="4" rowspan="2">  </td></tr><tr><td></td><td></td><td>②</td><td>Drawn</td><td>29.07.2014</td><td>Ray</td></tr><tr><td>Angle</td><td>±3°</td><td></td><td></td><td></td><td></td><td>Replace</td><td></td><td></td><td></td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td></td><td></td><td></td><td></td></tr></table>							Scale	FREE						Date	Name	Customer-No.	TOLERANCE						Drawn	29.07.2014	Amy		X.	±0.38					Approved	17.10.2014	Amy		X.X	±0.25									X.XX	±0.13									DIM	TOL	①	Update P/N to 22 pins version	17.10.2014	Ray							②	Drawn	29.07.2014	Ray	Angle	±3°					Replace				Angle	TOL	Id.	Modification	Date	Name					G
Scale	FREE						Date	Name	Customer-No.																																																																																					
TOLERANCE						Drawn	29.07.2014	Amy																																																																																						
X.	±0.38					Approved	17.10.2014	Amy																																																																																						
X.X	±0.25																																																																																													
X.XX	±0.13																																																																																													
DIM	TOL	①	Update P/N to 22 pins version	17.10.2014	Ray																																																																																									
		②	Drawn	29.07.2014	Ray																																																																																									
Angle	±3°					Replace																																																																																								
Angle	TOL	Id.	Modification	Date	Name																																																																																									
H	<table><tr><th>Positions</th><th>A</th><th>B</th><th>C</th><th>D</th></tr><tr><td>① 22</td><td>27.94</td><td>25.40</td><td>12.70</td><td>10.16</td></tr></table> <table><tr><td>ASS 6528 CO</td><td>rev01</td></tr><tr><td>Replace</td><td>Sheet</td></tr></table>							Positions	A	B	C	D	① 22	27.94	25.40	12.70	10.16	ASS 6528 CO	rev01	Replace	Sheet	H																																																																								
Positions	A	B	C	D																																																																																										
① 22	27.94	25.40	12.70	10.16																																																																																										
ASS 6528 CO	rev01																																																																																													
Replace	Sheet																																																																																													
	1	2	3	4	5	6	7																																																																																							