Part Number : 787231001
Product Description : 1.35mm Height Push-Pull micro-SIM Card Socket with Spring Tab, Surface Mount, 6 Circuits, Low-Halogen, Lead-Free
Series Number : 78723
Status : Active
Product Category : Memory / SIM Card Connectors



Documents and Resources

Drawings

787231001_sd.pdf

PK-78723-001-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-78723-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Memory / SIM Card Connectors
Series	78723
Description	1.35mm Height Push-Pull micro-SIM Card Socket with Spring Tab, Surface Mount, 6 Circuits, Low-Halogen, Lead-Free
Product Name	micro-SIM
Style	Push-Pull
UPC	887191064444

Electrical

Current - Maximum per Contact	0.5A
Shielded	Yes
Voltage - Maximum	5V DC

Physical

Card Detection Switch	No
Card Entry Location	Front
Circuits (Loaded)	6
Circuits (maximum)	6
Durability (mating cycles max)	500

Downloaded from Arrow.com.

Ejector Button Side	N/A
Material - Contact	Copper Alloy
Material - Plating Mating	Gold
Material - Shell	Stainless Steel
Net Weight	0.226/g
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	2.54mm
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount

Solder Process Data

Max-Duration	40
Lead-Free Process Capability	REFLOW
Max-Cycle	2
Max-Temp	250

Downloaded from Arrow.com.