


OD7015 Series



DC Fans - 12, 24V
70mm x 15.5mm (2.76" x 0.61")




Frame	PBT, UL94 V-0 Plastic	<u>Operating Temperature</u> -10°C ~ +70°C	STATIC PRESSURE ("H₂O) CFM
Impeller	PBT, UL94 V-0 Plastic	<u>Storage Temperature</u> -40°C ~ +70°C	
Connection	2x Lead Wires, 24 AWG	<u>Life Expectancy</u> 70,000 Hours (L10 at 40°C)	
Motor	Brushless DC, Auto Cutoff, Auto Restart, Electronically Protected, Polarity Protected	<u>Available Options</u> PWM Speed Control Input Tachometer Output Alarm Output IP Ratings	
Bearing System	Ball Bearings	Weight: 0.20 lbs.	
Dielectric Strength	500VDC/min, <1mA		
Insulation Resistance	≥10MΩ @ 500 VDC		

Part Number	Rated Voltage (Volts DC)	Voltage Range (Volts DC)	Input Power (Watts)(Max)	Rated Current (Amps)(Max)	Rated Speed (RPM)	Max Airflow (CFM)	Noise Level (dBA)	Max Static Pressure ("H ₂ O)
OD7015-12HHB	12	11.0 ~ 13.2	3.12 (4.32)	0.26 (0.36)	5000	35.7	48.2	0.26
OD7015-12MB	12	11.0 ~ 13.2	1.20 (2.16)	0.10 (0.18)	3500	23.4	36.3	0.13
OD7015-24HHB	24	22.0 ~ 26.4	5.04 (6.00)	0.21 (0.25)	5000	35.7	48.2	0.26


OD7015 Series with Tachometer




DC Fans - 12, 24V
70mm x 15.5mm (2.76" x 0.61")



Frame	PBT, UL94 V-0 Plastic	Operating Temperature -10°C ~ +70°C
Impeller	PBT, UL94 V-0 Plastic	Storage Temperature -40°C ~ +70°C
Connection	3x Lead Wires, 24 AWG	Life Expectancy 70,000 Hours (L10 at 40°C)
Motor	Brushless DC, Auto Cutoff, Auto Restart, Electronically Protected, Polarity Protected	Installed Options Open Collector Tach Output
Bearing System	Ball Bearings	Available Options 5V TTL Tach Output
Dielectric Strength	500VDC/min, <1mA	Weight: 0.20 lbs.
Insulation Resistance	≥10MΩ @ 500 VDC	



Part Number	Rated Voltage (Volts DC)	Voltage Range (Volts DC)	Input Power (Watts)(Max)	Rated Current (Amps)(Max)	Rated Speed (RPM)	Max Airflow (CFM)	Noise Level (dBA)	Max Static Pressure ("H ₂ O)
OD7015-12HHB01A	12	11.0 ~ 13.2	3.12 (4.32)	0.26 (0.36)	5000	35.7	48.2	0.26
OD7015-12MB01A	12	11.0 ~ 13.2	1.20 (2.16)	0.10 (0.18)	3500	23.4	36.3	0.13
OD7015-24HHB01A	24	22.0 ~ 26.4	5.04 (6.00)	0.21 (0.25)	5000	35.7	48.2	0.26



Tach Max Pullup Voltage: Fan Vcc
Tach Max Sink Current: 5mA
Tach Cycles per Rotation: 2