

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

LOC	DIST
J	—

REVISIONS 変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
#	L2	REVISED PER ECR-20-009164	14AUG2020	MK	DH







VIEW A-A

NOTE:


1. MATING TAB THICKNESS IS 0.53–0.48
2. △2 STRESS RELIEVING
   FINISH IS SUBJECT TO CHANGE BY THE TYPE OF STRESS RELIEVING PROCESS
   * INERT GAS FURNACE.....MATTE
   * ATMOSPHERIC FURNACE FOLLOWING BY ACID PICKLE...BRIGHT




SECT. "B"-"B"
(-6 ONLY)



SECT. "B"-"B"



SECT. "C"-"C"



▲	108-5178	—#—	BRASS 0.32t	ELECTRICAL TIN PLATED WITHOUT STRESS RELIEVE	170037-9
	108-5178	—#—	BRASS 0.32t	ELECTRICAL TIN PLATED	170037-6
	108-5178	170038-5	PRE-TIN BRASS		170037-5
	108-5178	170038-4	PHOSBRO 0.32t	ELECTRICAL TIN PLATED	170037-4
	108-5178	170038-3	PHOSBRO 0.32t	—#— △2	170037-3
	108-5178	170038-2	BRASS 0.32t	ELECTRICAL TIN PLATED	170037-2
0.53–0.48	108-5008	170038-1	BRASS 0.32t	—#— △2	170037-1
MATING TAB THK.	PRODUCT SPEC NO.	L.P P/N	MATERIAL	FINISH	P/N

WIRE RANGE: 0.5~1.42 mm² (AWG #20~ #16)	THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN: LI HELEN 27AUG2004	TE Connectivity
INSULATION DIA: 2.29~3.3	DIMENSIONS: 単位： 粍 mm	CHK: Mikio Shindo 30 Aug. 04	NAME 名称: 187 SERIES FASTON RECEPTACLE —
TOLERANCES: ±0.4	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 0 PLC ± – 1 PLC ± – 2 PLC ± – 3 PLC ± – 4 PLC ± – ANGLES ± –	APVD: Mikio Shindo 30 Aug. 04	SIZE: A3 / CAGE CODE: 00779 / DRAWING NO 番号: C-170037 / RESTRICTED TO: —
	MATERIAL 材料: SEE TABLE	PRODUCT SPEC 製品規格: 108-5008	
	FINISH 仕上: SEE TABLE	APPLICATION SPEC 取付適用規格: 114-5084	
		WEIGHT: 0.35g/ea	CUSTOMER DRAWING / SCALE 尺度: 4:1 / SHEET: 1 OF 1 / REV: L2

Downloaded from Arrow.com.