



C2G
Discontinued - 12ft (3.7m) 16 AWG Hospital Grade Power Cord (NEMA 5-15P to IEC320C13R) - Gray with Clear Connectors (TAA Compliant)
Part No. 48050



Power cords used in hospitals and other medical settings must conform to strict standards for grounding reliability, assembly integrity, strength and durability, as well as regulatory standards such as NEMA and IEC specifications. These standards are in place to ensure that power cords are safe and reliable for use in demanding hospital environments. The hospital grade power cord selection from C2G, formerly Cables To Go, offers one of the broadest selections available on the market.

From our vast selection, you'll find the right solution for replacing an overused or misplaced power cord, or to optimize office or lab layout with a cable that is the perfect length needed. This cable, from our universal C13 series collection, will work with most PCs, monitors, scanners, printers and many other devices that are powered via the industry standard 3-pin C14 connector inlet.

The female C13R connector plugs directly into the device while the male hospital grade 5-15P connector plugs into a hospital grade supply outlet. The black connectors match almost any environment or hospital standard. Performance is guaranteed through a lifetime warranty so performance is never an issue. Easily recognizable with the Green Dot mark, this hospital grade power cord ensures compliance and delivers maximum performance.

Features & Benefits

5-15P male plug to c13R female plug for connecting to most PCs, monitors, scanners, printers and many other devices	Hospital grade reliability, assembly integrity, strength and durability
Green Dot indicating hospital grade	Conforms to NEMA and IEC specifications

Specifications

General Info

Product Line	C2G	Replaced by Part Number	48052
Color	Gray	UPC Number	757120480501
Country Of Origin	Taiwan, Province Of China	Application Sector	Commercial
Warranty Type	Lifetime	Type	Power Cord

Dimensions

Product Length US	12.0 FT	Cable Length	12 ft
-------------------	---------	--------------	-------

Trade Programs

TAA Compliant	Yes
---------------	-----

Technical Information

Wire Gauge	16 AWG	Jacket Rating	SVT Rated
Amperage	13 A	Connector 2	C13 IEC
Connector 1	NEMA 5-15 Male	Voltage	125.0 V