



	1	2	3	4	5	6	7																																																																											
A	AGAL 09/GP-N AGAL 09/GP/ME							A																																																																										
B	  TECHNICAL SPECIFICATION: Material: UL94V-0 ABS Operating Temperature: -55°C to +110°C Thumbscrews: Short, UNC 4-40 Features: Available in sizes 9-15-25-37-50 Version: -N = Black /ME = Metalized							B																																																																										
C								C																																																																										
D	 <table><tr><th>Item</th><th>QTY</th><th>Part description</th></tr><tr><td>1</td><td>1</td><td>CA09-Upper cover -N = Black /ME = Metalized</td></tr><tr><td>2</td><td>1</td><td>CA09-Lower cover -N = Black /ME = Metalized</td></tr><tr><td>3</td><td>4</td><td>TEL004 Screw</td></tr><tr><td>4</td><td>1</td><td>CA09CC-9Way Clamps</td></tr><tr><td>5</td><td>2</td><td>TAS (4.40) Short Jackscrews</td></tr></table>							Item	QTY	Part description	1	1	CA09-Upper cover -N = Black /ME = Metalized	2	1	CA09-Lower cover -N = Black /ME = Metalized	3	4	TEL004 Screw	4	1	CA09CC-9Way Clamps	5	2	TAS (4.40) Short Jackscrews	D																																																								
Item	QTY	Part description																																																																																
1	1	CA09-Upper cover -N = Black /ME = Metalized																																																																																
2	1	CA09-Lower cover -N = Black /ME = Metalized																																																																																
3	4	TEL004 Screw																																																																																
4	1	CA09CC-9Way Clamps																																																																																
5	2	TAS (4.40) Short Jackscrews																																																																																
E								E																																																																										
F								F																																																																										
G	RoHS compliant							G																																																																										
H	<table><tr><td>Scale</td><td>1:1</td><td></td><td></td><td></td><td></td><td></td><td>Customer-No.</td></tr><tr><td>TOLERANCE</td><td></td><td>⑤</td><td>change of plant</td><td>25.05.2017</td><td>S.Bölling</td><td>Drawn</td><td>17.04.2007</td><td>N.Schulz</td><td>ASSMANN WSW-No.</td></tr><tr><td>X.</td><td>±X</td><td>④</td><td>add dimension (hole diameter)</td><td>05.05.2014</td><td>A. Plate</td><td>Approved</td><td>24.09.2009</td><td>Helwig</td><td>AGAL xx/GP-N</td></tr><tr><td>X.X</td><td>±X</td><td>③</td><td>Modifly drawing</td><td>24.09.2009</td><td>Dean</td><td></td><td></td><td></td><td>AGAL xx/GP/ME</td></tr><tr><td>X.XX</td><td>±X</td><td>②</td><td>Update</td><td>02.07.2009</td><td>Dean</td><td></td><td></td><td></td><td></td></tr><tr><td>X°</td><td>±X</td><td>①</td><td>Zeichnungs Angleichung</td><td>17.04.2007</td><td>N.Schulz</td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td></td><td></td><td></td><td></td></tr></table>  <table><tr><td>Drawing-No.</td><td>ASS 1077 CO</td><td>rev05</td></tr><tr><td>Replace</td><td></td><td>Sheet 1/5</td></tr></table>							Scale	1:1						Customer-No.	TOLERANCE		⑤	change of plant	25.05.2017	S.Bölling	Drawn	17.04.2007	N.Schulz	ASSMANN WSW-No.	X.	±X	④	add dimension (hole diameter)	05.05.2014	A. Plate	Approved	24.09.2009	Helwig	AGAL xx/GP-N	X.X	±X	③	Modifly drawing	24.09.2009	Dean				AGAL xx/GP/ME	X.XX	±X	②	Update	02.07.2009	Dean					X°	±X	①	Zeichnungs Angleichung	17.04.2007	N.Schulz							Id.	Modification	Date	Name					Drawing-No.	ASS 1077 CO	rev05	Replace		Sheet 1/5	H
Scale	1:1						Customer-No.																																																																											
TOLERANCE		⑤	change of plant	25.05.2017	S.Bölling	Drawn	17.04.2007	N.Schulz	ASSMANN WSW-No.																																																																									
X.	±X	④	add dimension (hole diameter)	05.05.2014	A. Plate	Approved	24.09.2009	Helwig	AGAL xx/GP-N																																																																									
X.X	±X	③	Modifly drawing	24.09.2009	Dean				AGAL xx/GP/ME																																																																									
X.XX	±X	②	Update	02.07.2009	Dean																																																																													
X°	±X	①	Zeichnungs Angleichung	17.04.2007	N.Schulz																																																																													
		Id.	Modification	Date	Name																																																																													
Drawing-No.	ASS 1077 CO	rev05																																																																																
Replace		Sheet 1/5																																																																																
1	2	3	4	5	6	7																																																																												

TECHNICAL SPECIFICATION:

Material: UL94V-0 ABS
 Operating Temperatur: -55°C to +110°C
 Thumbscrews: Short, UNC 4-40

Features:
 Available in sizes 9-15-25-37-50

Version:
 -N = Black
 /ME = Metalized

Item	QTY	Part description
1	1	CA09-Upper cover -N = Black /ME = Metalized
2	1	CA09-Lower cover -N = Black /ME = Metalized
3	4	TEL004 Screw
4	1	CA09CC-9Way Clamps
5	2	TAS (4.40) Short Jackscrews

