




Automotive Parts > Automotive Connector Accessories > Automotive Connector Caps & Covers



Number of Positions: 25

Primary Product Color: **Black**

Protection & Strain Relief Accessory Type: **Cover**

Primary Product Material: **Polyamide 6.6 GF**

Cable Exit Angle: **90°**

Features

Product Type Features

Sealable	No
Protection & Strain Relief Accessory Type	Cover

Configuration Features

Number of Positions	25
---------------------	----

Body Features

Primary Product Color	Black
Primary Product Material	Polyamide 6.6 GF
Cable Exit Angle	90°

Mechanical Attachment

Strain Relief	Without
---------------	---------

Dimensions

Compatible Cable Bundle Diameter Range	13 mm[.512 in]
--	----------------

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-30 – 125 °C[-22 – 257 °F]

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features



Packaging Method	Box
------------------	-----

Other

Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-T4827-CH8172
Timer Connector Housing



Also in the Series | Junior Power Timer

Automotive Connector Caps & Covers (12)	Automotive Connector Locks & Position Assurance(15)	Automotive Housings(186)	Automotive Seals & Cavity Plugs(32)
Automotive Signal & Power Connector Housings(136)	Automotive Terminals(110)	Other Automotive Connector Accessories(1)	Special Purpose Terminals(2)

Also in the Series | Timer Connector System

Automotive Connector Caps & Covers (12)	Automotive Housings(186)	Automotive Signal & Power Headers(6)	Automotive Terminals(110)
Crimp Terminal Housings(13)	Quick Disconnects(4)		

Customers Also Bought




TE Part #A39093-000
B-155-11



TE Part #61863-2
RING CRIMP 18-14 AWG TPBR



TE Part #66400-3
III+ PIN,24-20,15AU/FL,LP



TE Part #163082-2
062 PIN ASS. TYP3+



TE Part #180430-2
250 FASTON,FLAG,REC.,20-16 AWG, TPBR



TE Part #180984
FASTON 250 BOOT FLAG NYLON NAT



TE Part #182916-1
CPC SQ.FL.RCPT STD SEX



TE Part #770377-1
UMNL II KEYING PLUG



TE Part #794275-1
06P UMNL INTERFACE SEAL



TE Part #2-1823498-1
62POS, MIXED, REC HSG, ASSY, SEALED

Documents

Product Drawings

COVER FOR 25W. SPLASH PROOF CO

English

CAD Files

Customer View Model

ENG_CVM_281812-1_5.3d_igs.zip

English

Customer View Model

ENG_CVM_281812-1_5.3d_stp.zip

English

Customer View Model

ENG_CVM_281812-1_5.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Product Specification

English

2-7-15 WAY SPLASE-PROOF CONNECTORS

English