

## Technical data sheet

Article number:  
323-00103

MA40-16/5



<b>Product Group</b>	Heat shrinkable tubing 4:1 - Flame retardant
<b>Product Family</b>	MA40 - medium wall adhesive lined
<b>Material</b>	Polyolefin, cross-linked (PO-X)
<b>Colour</b>	Black (BK)
<b>Adhesive</b>	Hot melt adhesive
<b>Dielectric Strength [Test method]</b>	15 kV/mm [IEC 60243-1]
<b>Elongation at break (min.) [Test method]</b>	350 % [ASTM D2671]
<b>Elongation At Heat Aging</b>	300 %
<b>Heat Aging Test [Test method]</b>	168h/150°C [ASTM D2671]
<b>Longitudinal Change After Shrinkage</b>	-10% max.
<b>Min. Shrink Temperature - °C</b>	+120 °C
<b>Minimum Tensile Strength At Heat Aging</b>	12 MPa
<b>Operating Temperature</b>	-55 °C to +110 °C
<b>Package Content</b>	160 m
<b>Package Content packed in</b>	lengths
<b>Recov. Ø d max.</b>	5.0 mm
<b>Shrink Ratio</b>	up to 4:1
<b>Supplied Ø D min.</b>	16.0 mm
<b>Tensile Strength [Test method]</b>	12 MPa [ASTM D2671]
<b>Wall (WT)</b>	2.00 mm

RoHS 