




REV.	DATE	ECR NO.	DESCRIPTION
NC	05/18/99	XXXXXX	INITIAL RELEASE
A	05/26/11	XXXXXX	UPDATE DRAWING FORMAT
B	07/15/11	2199	ECR 2199
C	03/15/13	2435	ADD RECOMMENDED PCB LAYOUT, ADD ELECTRICAL SPEC. UPDATE DRAWING FORMAT
D	07/31/13	2505	MODIFY RECOMMENDED PCB LAYOUT



RECOMMENDED MOUNTING PATTERN

1. IMPEDANCE: 50 OHM
2. FREQUENCY RANGE: 0-6 GHZ
3. VSWR: 1.3 MAX.
3. DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS, MIN.
4. DURABILITY: 500 CYCLES MIN.
5. TEMPERATURE RANGE: -65°C TO +165°C

3	CONTACT PIN	BER. COPPER	GOLD	1
2	INSULATOR	PTFE	NATURAL	1
1	BODY	BRASS	GOLD	1
	DESCRIPTION	MATERIAL	FINISH	QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: <0.5 ± 0.05mm 0.5 - 6mm ± 0.10mm 6 - 30mm ± 0.20mm 30 - 120mm ± 0.30mm ANGLES ± 1° UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: <.020 ± 0.002" .020 - .236 = ± 0.004" .236 - 1.180 = ± 0.007" 1.180 - 4.724 = ± 0.012" ANGLES ± 1° DO NOT SCALE DRAWING

APPROVALS	DATE
DRAWN M.ZHANG	07/31/13
CHECKED	
ISSUED	
SHEET 1 OF 1	
CAD FILE C:/CONNEX/262109.DWG	

Amphenol Connex			
PART DESCRIPTION			
MMCX SURFACE MOUNT JACK			
PART NO. 262109			
DWG. NO. 262109.DWG	REV. D	SIZE A	SCALE NA