



✓ Active

TE CONNECTIVITY (TE)

55A1113-20-9-9

Raychem | RC , SP

55A1113-20-9-9

TE Internal Number: 556070-000

Alias ID: 6-1194386-9

EU RoHS Compliant

EU ELV Compliant

Cable Type Spec 55

Conductor Diameter 1.01 mm [.04 in]

Number of Strands 19

Strand Size (AWG) 32

Overall Outside Diameter 2.13 mm [.084 in]

 **PRODUCT DRAWING**

English

DOCUMENTATION

Product Drawings

CABLE, ELECTRIC, RADIATION-CROSSLINKED, EXTRUDED, MODIFIED, FLUOROPOLYMER-INSULATED, ONE CONDUCTOR, SHIELDED, JACKETED, LIGHTWEIGHT

PDF

English

Product Specifications

Product Specification

Wire And Cable, Electric, Radiation-Crosslinked, Extruded, Modified, Fluoropolymer-Insulated Copper Or Copper Alloy

PDF

English

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Type Spec 55

Shielded Yes

Cable Style Jacketed, Round Braided

Product Type Cable

Product Classification Cable - High Performance - Spec 44, 55 & RCW

Configuration Features

Number of Strands 19

Number of Conductors 1

Electrical Characteristics

Voltage Rating (V) 600

Body Features

Shield Material Nickel-Coated Copper

Jacket Color White

Wire Color White

Conductor Material Nickel-Plated Copper

Shield Diameter 1.75 mm [.069 in]

Shield Size (AWG) 38

Dimensions

Conductor Diameter 1.01 mm [.04 in]

Strand Size (AWG) 32

Overall Outside Diameter 2.13 mm [.084 in]

Wire Size (AWG) 20

Wire Size (mm²) .5176

Wire Diameter 1.27 mm [.05 in]

Usage Conditions

Operating Temperature Range (°C) -65 – 200

Other

Wire Source United Kingdom, United States

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF

