





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/11/14	
A		ADDED OPERATING VOLTAGE RATING	10/7/15	
B		UPDATE P1 DIRECTION	12/7/15	AY/OC
C		UPDATE SPEC.	5/29/18	AY/SL
D		UPDATE DIM.	8/31/20	LH/EY



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:
 Insulator: Nylon PA66, rated UL 94V-0
 Insulator color: White
 Contacts: Brass
 Plating:
 Gold flash over Nickel underplate overall
 Electrical:
 Current rating: 7.0 Amp
 Contact Resistance: 20 mohms max.
 Insulation resistance: 1,000 Mohms min
 Dielectric withstanding voltage: 1,000 VAC for 1 minute
 Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant



Positions: 2 thru 20

A = .156 [3.96] x No. of Positions

B = .156 [3.96] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ±.10 .XX ± .020 Ø.XX ±.015 .XXX ± .015 Ø.XXX ±.010			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS			DATE		TITLE .156 [3.96] HEADER, STRAIGHT, GOLD FLASH PLATED	
DRAWN		HR	9/11/14			
CHECKED		TW	9/11/14			
APPROVED						
REF: S00019C		SCALE: NTS		SHEET 1 OF 1		