
molex



Part Number : 15916143
Product Description : 2.54mm Pitch C-Grid Breakaway Header, Surface Mount, Dual Row, Vertical, 14 Circuits, 0.76µm Gold (Au) Selective Plating, without PCB Locator Pegs, Tape and Reel
Series Number : 71308
Status : Active
Product Category : PCB Headers and Receptacles
Engineering Part Number : 71308-1714N

Documents and Resources

Drawings

015916143_sd.pdf

713080000-PK-000.pdf

713080001-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

713080001-AS-000.pdf

PS-71308-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

Downloaded from Arrow.com.

EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	71308
Description	2.54mm Pitch C-Grid Breakaway Header, Surface Mount, Dual Row, Vertical, 14 Circuits, 0.76µm Gold (Au) Selective Plating, without PCB Locator Pegs, Tape and Reel
Application	Board-to-Board, Signal, Wire-to-Board
Component Type	PCB Header
Product Name	C-Grid
UPC	800753144125

Agency

CSA	LR19980
UL	E29179

Downloaded from Arrow.com.

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Physical

Breakaway	Yes
Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Black
Durability (mating cycles max)	50
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	No
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.843/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	No
Pitch - Mating Interface	2.54mm
Plating min - Mating	0.813µm
Plating min - Termination	2.032µm
Polarized to Mating Part	No
Polarized to PCB	No
Robotic Placement	Pick and Place Cap
Shrouded	Unshrouded
Stackable	Yes
Temperature Range - Operating	-40° to +120°C
Termination Interface Style	Surface Mount

Downloaded from Arrow.com.

Solder Process Data

Lead-Free Process Capability	REFLOW
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
C-Grid Right-Angle, Dual Row, Surface Mount PCB Receptacles	71979
C-Grid Vertical, Dual Row, High Profile, Surface Mount PCB Connectors	71395
C-Grid Vertical, Dual Row, High Profile, Through Hole PCB Receptacles	71850
2.54mm Pitch C-Grid Shunt Terminal Housings	7859

Downloaded from Arrow.com.