



BeStar Technologies Inc.

Address: 761 N. 17th Street Unit 4, St. Charles, IL 60174

Tel : 847-261-2850 E-mail : sales@bestartech.com Web : www.bestartech.com

Document Number : 0511-70
Revision : A3
Total Pages : 4
Prepare by : Loki, Lo
Date : 29 October, 2015

SoniCrest Brand Acoustic Components

www.jlsonicrest.com

Document Type : Specification
Product Type : Electro-magnetic Sound Generator Component
Part Number : HCM2505B

A1 - New issue created by Leo, Sin on 28 Nov., 2005		
A2 - Updated section 2 - 6 by Loki, Lo on 28 Oct., 2015		
A3 - Updated Mechanical Layout by Loki, Lo on 29 Oct., 2015		

This material is the property of BeStar Technologies Inc.
Unauthorized copying or use of this material is prohibited.

1. Purpose and Scope

This document contains both general requirements, qualification requirements, and those specific electrical, mechanical requirements for this part.

2. Description

Ø25mm electro-magnetic sound generator, RoHS compliant.

3. Application

Telecommunication Equipment, Computers and Peripherals, Portable Equipment, Automobile Electronics, etc.

4. Component Requirement

4.1. General Requirement

4.1.1. Operating Temperature Range	: -20°C to +70°C
4.1.2. Storage Temperature Range	: -30°C to +85°C
4.1.3. Weight	: Approx. 10g
4.1.4. Housing Material	: NORYL

4.2. Electrical Requirement

4.2.1. Rated Voltage	: 5V
4.2.2. Operating Voltage	: 3 ~ 8 V
4.2.3. Rated Current	: ≤70mA
4.2.4. Coil Resistance	: 36 ± 5 Ω
4.2.5. Rated Frequency	: 1000 ~ 1500Hz
4.2.6. Sound Pressure Level at 10cm (Applying 1000 ~ 1500Hz)	: ≥80dB

4.3. Mechanical Requirement

4.3.1. Layout and Dimension	: See Section 6, Figure 2
-----------------------------	---------------------------

4.4. Test Setup




Figure 1. Test Setup

Notes : Apply 2.5V_{0-p} from Signal Generator, set 1000Hz from Signal Generator. Measure SPL using a calibrated SPL meter 10cm from the sound port. Sound level meter to be in accordance with IEC651 (1979) Type 1 and/or ANSI S1.4-1983. The meter must be checked on a daily basis using a calibrated acoustic calibrator recommended by the manufacturer. Measurement should be carried out in a free field environment or at least 40cm from any surface.

5. Reliability Test

- 5.1. Operating Life** : Subject samples to room condition for 96 hours under rated voltage
- 5.2. High Temperature** : Subject samples to $+70 \pm 3 \text{ }^{\circ}\text{C}$ for 96 hours. Components must be fully stabilized at temperature extremes before data is taken, which may require up to a 2 hours soak.
- 5.3. Low Temperature** : Subject samples to $-20 \pm 3 \text{ }^{\circ}\text{C}$ for 96 hours. Components must be fully stabilized at temperature extremes before data is taken, which may require up to a 2 hours soak.
- 5.4. Temperature Shock** : Each temperature cycle shall consist of 1 hour at -20°C followed by 1 hour at $+70^{\circ}\text{C}$ with a 20 seconds maximum transition time between temperature extremes. Test duration is for 32 cycles.
- 5.5. Static Humidity** : Precondition at room temperature for 1 hour. Then expose to $+40^{\circ}\text{C}$ with 90% to 95% relative humidity for 96 hours. Finally dry at room ambient for 2 hours before taking final measurement.
- 5.6. Drop Test** : Drop samples naturally from the height of 1.5m onto a 10mm thickness wooden board in 3 directions (x, y and z).
- 5.7. Random Vibration** : Secure samples. Vibrated randomly 10 ~ 55Hz with 1.5mm peak amplitude in 3 directions (x, y and z). The test duration is 2 hours per plane.

6. Mechanical Layout

Unit : mm
Tolerance : Linear XX.X = ± 0.3
 XX.XX = ± 0.05
 Angular = $\pm 0.25^{\circ}$
(unless otherwise specified)




Figure 2. HCM2505B Mechanical Layout