




Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image







In some applications it makes sense to add a test point or a disconnect element to the feed through terminal for testing and safety purposes. With test disconnect terminals you measure electric circuits in the absence of voltage. While the disconnecting points clearance and creepage distance is not assessed in dimensional terms, the specified rated impulse voltage strength must be proven.

General ordering data

Version	Test-disconnect terminal, Tension-clamp connection, 2.5 mm², 500 V, 20 A, Pivoting, dark beige
Order No.	<u>8731720000</u>
Туре	ZTR 2.5/3AN
GTIN (EAN)	4032248404902
Qty.	50 ST



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals			
PP -			
Approvals	C € ® !	27 . FR	
ROHS	Conform		
UL File Number Search	<u>UL Website</u>		
Certificate No. (UR)	E60693		
Dimensions and weights			
Depth	38.5 mm	Depth (inches)	1.5157 inch
Depth including DIN rail	41 mm	Height	79.5 mm
Height (inches)	3.1299 inch	Width	5.1 mm
Width (inches)	0.2008 inch	Net weight	11.29 g
Temperatures			
Storage temperature	-25 °C55 °C	Ambient temperature	-5 °C40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C
Environmental Product Comp	oliance	<u> </u>	1
RoHS Compliance Status	Compliant without exemptio	n	
REACH SVHC	No SVHC above 0.1 wt%		
Material data			
Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0	Coloui	uark beige
· -			'
System specifications			
Version	Tension-clamp connection, 3 connections, Spacer, for plug-in cross-connector, One end without connector	End cover plate required	Yes
Number of potentials	1	Number of levels	1
Number of clamping points per level	3	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Rail PE function	TS 35	N-function	No
re lunction	No	PEN function	No
Additional technical data			
Open sides	right	Number of similar terminals	3
Installation advice	Direct mounting	Explosion-tested version	No
Type of mounting	Snap-on		
CSA rating data			
	40.4440		300 V
Wire cross section max. (CSA)	12 AWG	Voltage size C (CSA)	⊀()() \/

Creation date 06.07.2025 09:37:40 MEZ

10 A

300 V

26 AWG

Current size C (CSA)

Voltage size B (CSA)

Wire cross section min. (CSA)

Catalogue status / Drawings 2

Certificate No. (CSA)

Current size B (CSA)

200039-1152892

10 A



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Conductors for clamping (additional connection)

Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, max.

1.5 mm²

Connection type, additional connection Tension-clamp connection

Conductors	for clampi	ng (rated	connection)

Gauge to IEC 60947-1	A3		
Vire connection cross section AWG, nax.	AWG 12		
Connection direction	top		
Stripping length	10 mm		
ype of connection 2	Tension-clamp connection		
ype of connection	Tension-clamp connection		
lumber of connections	3		
Clamping range, max.	4 mm ²		
Clamping range, min.	0.05 mm ²		
Blade size	0.6 x 3.5 mm		
Vire connection cross section AWG, nin.	AWG 30		
Vire connection cross-section, finely tranded with wire-end ferrules DIN 16228/4, max.	2.5 mm ²		
Vire connection cross-section, finely tranded with wire-end ferrules DIN 16228/4, min.	0.5 mm ²		
Vire connection cross-section, finely tranded with wire-end ferrules DIN 16228/1, max.	2.5 mm ²		
Vire connection cross-section, finely tranded with wire-end ferrules DIN 16228/1, min.	0.5 mm ²		
Vire connection cross section, finely tranded, max.	4 mm ²		
Vire connection cross section, finely tranded, min.	0.5 mm ²		
Connection cross-section, stranded, nax.	4 mm²		
Connection cross-section, stranded, mi	n. 0.5 mm²		
Vire connection cross-section, solid core, max.	4 mm ²		
Vire connection cross-section, solid core, min.	0.5 mm ²		
ube length for wire-end ferrule with	Tube length	min.	6 mm
olastic collar DIN 46228/4		max.	10 mm
	Cross-section for conductor connection	nominal	0.5 mm ²
	Tube length	min.	6 mm
		max.	12 mm
	Cross-section for conductor connection	nominal	0.75 mm ²
	Tube length	min.	6 mm
		max.	12 mm
	Cross-section for conductor connection	nominal	1 mm²
	Tube length	min.	8 mm
		max.	12 mm
	Cross-section for conductor connection	nominal	1.5 mm ²
		min.	
	Tube length	111111.	8 mm
	Tube length	max.	12 mm

Creation date 06.07.2025 09:37:40 MEZ

Catalogue status / Drawings



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Tube length for wire-end ferrule without	Tuk
plastic collar DIN 46228/1	Cro
	Tub
	_

Tube length	nominal	10 mm
Cross-section for conductor connection	nominal	0.5 mm ²
Tube length	nominal	10 mm
Cross-section for conductor connection	nominal	0.75 mm ²
Tube length	nominal	10 mm
Cross-section for conductor connection	nominal	1 mm ²
Tube length	min.	10 mm
	max.	12 mm
Cross-section for conductor connection	nominal	1.5 mm ²
Tube length	min.	10 mm
	max.	12 mm
Cross-section for conductor connection	nominal	2.5 mm ²

Disconnect terminals

Slitting	Pivoting	Cross-disconnect	without
Integral test socket	Yes		

General

Wire connection cross section AWG,	AWG 12	Installation advice	Direct mounting
max.			
Wire connection cross section AWG,	AWG 30	Standards	IEC 60947-7-1
min.			
Rail	TS 35		

Rating data

Rated cross-section	2.5 mm ²	Rated voltage	500 V
Rated DC voltage	500 V	Rated current	20 A
Current at maximum wires	20 A	Standards	IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	1.33 mΩ	Rated impulse withstand voltage	6 kV
Power loss in accordance with IEC 60947-7-x	0.77 W	Pollution severity	3

UL rating data

Conductor size Factory wiring max. (UR) 12 AWG		Current size C (UR)	20 A
Voltage size C (UR)	600 V	Conductor size Factory wiring min. (UR)	30 AWG
Certificate No. (UR)	E60693	Conductor size Field wiring min. (UR)	30 AWG
Conductor size Field wiring max. (UR)	12 AWG		

Classifications

ETIM 6.0	EC000902	ETIM 7.0	EC000902
ETIM 8.0	EC000902	ETIM 9.0	EC000902
ETIM 10.0	EC000902	ECLASS 9.0	27-14-11-26
ECLASS 9.1	27-14-11-26	ECLASS 10.0	27-14-11-26
ECLASS 11.0	27-14-11-26	ECLASS 12.0	27-14-11-26
ECLASS 13.0	27-25-01-09	ECLASS 14.0	27-25-01-09
ECLASS 15.0	27-25-01-09		





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Drawings



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

2.5 mm²

2.5

mm²

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

Туре	ZQV 2.5/2	Version
Order No.	1608860000	Z-series, Cross-connector, 24 A
GTIN (EAN)	4008190123680	
Qty.	60 ST	
Туре	ZQV 2.5/3	Version
Order No.	<u>1608870000</u>	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190061630	
Qty.	60 ST	
Туре	ZQV 2.5/4	Version
Order No.	<u>1608880000</u>	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190082208	
Qty.	60 ST	
Туре	ZQV 2.5/5	Version
Order No.	<u>1608890000</u>	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190065713	
Qty.	20 ST	
Туре	ZQV 2.5/6	Version
Order No.	1608900000	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190149840	
Qty.	20 ST	
Туре	ZQV 2.5/7	Version
Order No.	1608910000	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190159665	
Qty.	20 ST	
Туре	ZQV 2.5/8	Version
Order No.	1608920000	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190061531	
Qty.	20 ST	
Туре	ZQV 2.5/9	Version
Order No.	1608930000	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190117009	
Qty.	20 ST	
Туре	ZQV 2.5/10	Version
Order No.	1608940000	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190099060	
Qty.	20 ST	
Туре	ZQV 2.5/20	Version
0 1 11		
Order No.	1908960000	Z-series, Cross-connector, For the terminals, Number of poles: 20
GTIN (EAN)	<u>1908960000</u> 4032248535293	Z-series, Cross-connector, For the terminals, Number of poles: 20
		Z-series, Cross-connector, For the terminals, Number of poles: 20

Data sheet

ZTR 2.5/3AN



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Туре	ZQV 2.5/50	Version
Order No.	1697540000	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190883256	· · · · · · · · · · · · · · · · · · ·
Qty.	10 ST	
Туре	ZAP/TW 3	Version
Order No.	1608800000	Z-series, Accessories, End plate, Partition plate
GTIN (EAN)	4008190190927	, ·,
Qty.	50 ST	
Туре	ZAP/TW 3 BL	Version
Order No.	1608810000	Z-series, End plate, Partition plate
GTIN (EAN)	4008190190934	2 sorts, and plate, i artifori plate
Qty.	50 ST	
Туре	ZAP/TW 3 GN	Version
Order No.	1683840000	Z-series, End plate, Partition plate
GTIN (EAN)	4008190477561	—, — p, — p
Qty.	50 ST	
Туре	ZAP/TW 3 GR	Version
Order No.	1683870000	Z-series, End plate, Partition plate
GTIN (EAN)	4008190477592	2 sorts, and plate, i artifori plate
Qty.	50 ST	
Туре	ZAP/TW 3 OR	Version
Order No.	1608820000	Z-series, End plate, Partition plate
GTIN (EAN)	4008190190941	2 ornos, End plate, i districti plate
Qty.	50 ST	
Туре	ZAP/TW 3 RT	Version
Order No.	1683820000	Z-series, End plate, Partition plate
GTIN (EAN)	4008190477547	
Qty.	50 ST	
Туре	ZAP/TW 3 SW	Version
Order No.	<u>1683890000</u>	Z-series, End plate, Partition plate
GTIN (EAN)	4008190477615	
Qty.	50 ST	
Туре	ZAP/TW 3 WS	Version
Order No.	1683880000	Z-series, End plate, Partition plate
GTIN (EAN)	4008190477608	
Qty.	50 ST	

SAK-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

General ordering data

Туре	EW 35	Version
Order No.	0383560000	End bracket, beige, TS 35, V-2, Wemid, Width: 8.5 mm, 100 °C
GTIN (EAN)	4008190181314	
Qty.	50 ST	
Туре	EW 35 GR 7032	Version
Order No.	0383530000	End bracket, grey, TS 35, V-0, Wemid, Width: 9 mm, 120 °C
GTIN (EAN)	4008190027322	
Qty.	50 ST	
Туре	EW 35/SCHA/M3	Version
Order No.	0258660000	End bracket, beige, TS 35, V-2, Wemid, Width: 16.5 mm, 100 °C
GTIN (EAN)	4008190033477	
Qty.	20 ST	

W-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Туре	WEW 35/1	Version
Order No.	<u>1059000000</u>	End bracket, dark beige, TS 35, V-2, Wemid, Width: 12 mm, 100 °C
GTIN (EAN)	4008190172282	
Qty.	50 ST	
Туре	WEW 35/2	Version
Type Order No.	WEW 35/2 1061200000	Version End bracket, dark beige, TS 35, HB, Wemid, Width: 8 mm, 100 °C
	,	

Z-Series

Z Series Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

	- · · J · · · ·	
Туре	ZEW 35	Version
Order No.	9540000000	End bracket, dark beige, TS 35, V-2, Wemid, Width: 6 mm, 100 °C
GTIN (EAN)	4008190956264	
Otv	20 ST	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Туре	ZEW 35/2	Version
Order No.	<u>8630740000</u>	End bracket, dark beige, TS 35, V-2, Wemid, Width: 8 mm, 100 °C
GTIN (EAN)	4032248348916	
Qty.	20 ST	
Туре	ZTA 1	Version
Order No.	<u>1609040000</u>	Accessories, Test adapter, 9 A
GTIN (EAN)	4008190196851	
Qty.	25 ST	
Туре	ZTA 1/ZA	Version
Order No.	1609050000	Accessories, Test adapter, 9 A
GTIN (EAN)	4008190206543	
Qty.	25 ST	

Test plugs



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

Туре	PS 2.3 RT	Version
Order No.	<u>0180400000</u>	Test adapter (terminal), 230 V, 20 mA
GTIN (EAN)	4008190060121	
Qty.	20 ST	

Fuse holder



The fuse holder SIHA quickly turns a disconnect terminal into a fuse terminal: simply remove the disconnect lever and attach the fuse unit.

General ordering data

Туре	SIHA 3/G20/LD 10-36V	Version
Order No.	<u>7921570000</u>	Fuse holder for feed-through modular terminal, black, 2.31 mA,
GTIN (EAN)	4032248322503	pluggable, V-0, Wemid
Qty.	25 ST	
Туре	SIHA 3/G20/LD 35-70V	Version
Type Order No.	SIHA 3/G20/LD 35-70V 7921580000	Version Fuse holder for feed-through modular terminal, black, 2.31 mA,
	, ,	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Туре	SIHA 3/G20/LD 60-150V	Version
Order No.	<u>7921590000</u>	Fuse holder for feed-through modular terminal, black, 2.31 mA,
GTIN (EAN)	4032248322626	pluggable, V-0, Wemid
Qty.	25 ST	
Туре	SIHA 3/G20/LD 140-250V	Version
Type Order No.	SIHA 3/G20/LD 140-250V 7921600000	Version Fuse holder for feed-through modular terminal, black, 2.31 mA,
	, ,	

Component plugs



The component plug is used to integrate an electrical component in a disconnect terminal block. After soldering the electronic component, the plug can be integrated into the disconnection area of our disconnect terminal blocks and thus changes the disconnect terminal block into a modular terminal block with integrated electronic component.

General ordering data

Туре	BEST	Version
Order No.	<u>1833100000</u>	Accessories, Component plug
GTIN (EAN)	4032248501014	
Qty.	50 ST	
Туре	BEST/D	Version
Order No.	<u>1878560000</u>	Accessories, Component plug, 1 A
GTIN (EAN)	4032248471492	
Qty.	50 ST	
Туре	BEST/DRBR	Version
Order No.	<u>1878570000</u>	Accessories, Component plug, 22 A
GTIN (EAN)	4032248471508	
Qty.	50 ST	

Disconnect plugs



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

General ordering data

Туре	TNST	Version
Order No.	1833090000	Accessories, Disconnect plug, 20 A
GTIN (EAN)	4032248471485	
Qty.	50 ST	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Z-Series

Z

Series

The use of reducing sleeves simplifies the connection of conductors with smaller cross-sections. Conductors can be reliably inserted into the clamping point without the strands fraying. The use of a reducing sleeve centres the conductor in the entry point.

General ordering data

Туре	ZRH 2.5/1 WS	Version
Order No.	<u>1614300000</u>	Z-series, Reducing sleeve
GTIN (EAN)	4008190206789	
Qty.	1000 ST	
Туре	ZRH 2.5/2 GR/V0	Version
Order No.	<u>1614290000</u>	Z-series, Reducing sleeve
GTIN (EAN)	4008190072476	
Qty.	1000 ST	
Туре	ZRH 2.5/3	Version
Order No.	<u>1614280000</u>	Z-series, Reducing sleeve
GTIN (EAN)	4008190206796	
Qty.	1000 ST	

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	DEK 5/5 MC NE WS	Version
Order No.	1609801044	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190397111	Weidmueller, white
Qty.	1000 ST	
Туре	WS 10/5 M MC NE WS	Version
Type Order No.	WS 10/5 M MC NE WS 1792000000	Version WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
	,	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Туре	,	WS 10/5 MC NE WS	Version	
Order	No.	<u>1635000000</u>	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,	
GTIN	(EAN)	4008190261948	Allen-Bradley, white	
Qty.		720 ST		

Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snaped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

General ordering data

Туре	BZT 1 WS 10/5	Version
Order No.	<u>1805490000</u>	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 ST	
Туре	BZT 1 ZA WS 10/5	Version
Order No.	<u>1805520000</u>	Accessories, Marker holder
GTIN (EAN)	4032248270248	
Qty.	100 ST	

Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Туре	SDIS SLIM 0.6X3.5X100	Version
Order No.	2749610000	Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade
GTIN (EAN)	4050118896350	thickness (A): 0.6 mm
Qty.	1 ST	

Data sheet

ZTR 2.5/3AN



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories



General ordering data

Type DTLE 2.5/4
Order No. 2910530000
GTIN (EAN) 4099986519466

Qty. 25 ST

Version

Locking element (terminal), Wemid, red