


## Sleeve Holds 1 High-Density Fiber Cassette, 0U

MODEL NUMBER: N482-00U



Mounts a single fiber cassette to a rack without the extra expense of a 1U chassis or to an area without an existing rack infrastructure, including remote workstations, new build-outs and temporary applications.

### Description

The N482-00U High-Density Fiber Cassette Sleeve is a cost-effective solution for adding a single N482-Series fiber cassette to your network application without buying a chassis. Made of heavy-duty cold-rolled steel, this space-saving 0U sleeve mounts to the metal surface of your EIA-standard 19-inch rack or cable manager via two attached magnets.

The N482-00U is recommended for adding an extra cassette to a rack application without the expense of a new 1U chassis, as well as adding fiber connectivity where no existing rack infrastructure exists, such as a remote workstation, new build-out or temporary install location. It reduces cable clutter by allowing you to connect cables at the cable manager through which they are being routed.

The N482-00U accommodates N482-Series cassettes, including LC and MTP/MPO connector types. It allows you to connect 10 GbE, 40 GbE and 100/120 GbE network equipment with elegance, ease and little cost. The fully passive sleeve adds no heat or cooling load.

### Features

#### Cost-Effective, Space-Saving Solution for Adding a Fiber Cassette to Your System

- Holds a single N482-Series fiber cassette
- Attaches to metal rack enclosures and cable managers with included magnets
- Expands an installation without purchasing a new 1U chassis
- Adds network connectivity to areas without existing infrastructure
- Ideal for connecting 10 GbE, 40 GbE and 100/120 GbE network equipment
- Connects cables at cable manager through which they're being routed
- Fully passive with no added heat or cooling load
- Made from heavy-duty cold-rolled steel

## Specifications

OVERVIEW	
UPC Code	037332202451
Accessory Type	Pass-Through Panel

### Highlights

- Holds a single N482-Series cassette
- Mounts to metal surface via attached magnets
- Made from heavy-duty cold-rolled steel
- No added heat or cooling load
- Ideal for connecting 10, 40 and 100/120 GbE equipment

### Package Includes

- High-Density Fiber Cassette Sleeve, 0U, 1-Cassette Capacity



Powering Business Worldwide

TRIPP LITE  
SERIES

Technology	Multimode
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / in.)	2.00 x 4.60 x 10.40
Shipping Dimensions (hwd / cm)	5.08 x 11.68 x 26.42
Shipping Weight (lbs.)	0.80
Shipping Weight (kg)	0.36
Unit Dimensions (hwd / in.)	2.000 x 4.600 x 10.400
Panel Style	Cassette Type
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 122°F (-20° to 50°C)
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.