

Alchip™-MZL Series

Upgrade!

- Low ESR, 5,000hours at 105°C
- Rated voltage range : 6.3 to 50V, Nominal capacitance range : 100 to 1,500μF
- Solvent resistant type(see PRECAUTIONS AND GUIDELINES)
- Vibration resistance structure
- RoHS2 Compliant
- AEC-Q200 compliant : Please contact Chemi-Con for more details, test data, information.

MZL
↑ Longer life
MZA/MZR




SPECIFICATIONS

Items	Characteristics									
Category	-55 to +105℃									
Temperature Range										
Rated Voltage Range	6.3 to 50V _{dc}									
Capacitance Tolerance	±20% (M) (at 20℃, 120Hz)									
Leakage Current	I=0.01CV or 3μA, whichever is greater. Where, I : Max. leakage current (μA), C : Nominal capacitance (μF), V : Rated voltage (V) (at 20℃ after 2 minutes)									
Dissipation Factor (tan δ)	Rated voltage (V _{ac})	6.3V	10V	16V	25V	35V	50V	(at 20℃, 120Hz)		
	tan δ (Max.)	0.26	0.19	0.16	0.14	0.12	0.10			
Low Temperature Characteristics (Max. Impedance Ratio)	Rated voltage (V _{ac})	6.3V	10V	16V	25V	35V	50V	(at 120Hz)		
	Z(-25℃)/Z(+20℃)	2	2	2	2	2	2			
	Z(-40℃)/Z(+20℃)	3	3	3	3	3	3			
	Z(-55℃)/Z(+20℃)	4	4	4	3	3	3			
Endurance	The following specifications shall be satisfied when the capacitors are restored to 20℃ after the rated voltage is applied for 5,000 hours at 105℃.									
	Capacitance change	≤ ±35% of the initial value								
	D.F. (tan δ)	≤300% of the initial specified value								
	Leakage current	≤The initial specified value								
Shelf Life	The following specifications shall be satisfied when the capacitors are restored to 20℃ after exposing them for 1,000 hours at 105℃ without voltage applied. Before the measurement, the capacitor shall be preconditioned by applying voltage according to Item 4.1 of JIS C 5101-4.									
	Capacitance change	≤ ±30% of the initial value								
	D.F. (tan δ)	≤200% of the initial specified value								
	Leakage current	≤The initial specified value								
Surge Voltage Test	The capacitors shall be subjected to 1,000 cycles each consisting of charging with the specified surge voltage for 30±5 seconds through a protective resistor (as required for RC=0.1±0.05sec) and open-circuiting for 5.5 minutes at a room temperature of 15 to 35℃.									
	Rated voltage (V _{ac})	6.3	10	16	25	35	50			
	Surge voltage (V _{ac})	7.2	12	18	29	40	58			
	Appearance	No significant damage								
	Capacitance change	≤ ±20% of the initial value								
	D.F. (tan δ)	≤200% of the initial specified value								
	Leakage current	≤The initial specified value								
	(Caution)									
	Surge Voltage Test intends to evaluate capacitors in durability of an exceptional excessive voltage under specific conditions.It does not imply long-term use at all.									

DIMENSIONS [mm]

● Terminal Code : A

● Terminal Code : G(Vibration resistant structure)



Size code	D	L	A	B	C	W	P
HA0	8	10.0	8.3	8.3	9.0	0.7 to 1.1	3.1
JA0	10	10.0	10.3	10.3	11.0	0.7 to 1.1	4.5

MARKING

EX) 35V560μF




● Rated voltage symbol

Rated voltage (V _{dc})	6.3	10	16	25	35	50
Symbol	j	A	C	E	V	H

Applying voltage over the rated voltages causes the capacitors to have short lifetime. Besides, applying voltage over the specified surge voltages may cause to have short circuit failure. A protection circuit should be used if applied voltage will exceed the rated voltages.



◆PART NUMBERING SYSTEM



Please refer to "Product code guide (surface mount type)"

◆STANDARD RATINGS

WV (V _{dc})	Cap (μF)	Size code	tan δ	ESR (Ω max./20°C, 100kHz)	Rated ripple current (mA rms/105°C, 100kHz)	Part No.
6.3	470	HA0	0.26	0.16	600	EMZL6R3□RA471MHA0G
	1,000	HA0	0.26	0.16	600	EMZL6R3□RA102MHA0G
	1,500	JA0	0.26	0.08	850	EMZL6R3□RA152MJA0G
10	330	HA0	0.19	0.16	600	EMZL100□RA331MHA0G
	470	HA0	0.19	0.16	600	EMZL100□RA471MHA0G
	680	HA0	0.19	0.16	600	EMZL100□RA681MHA0G
	1,000	JA0	0.19	0.08	850	EMZL100□RA102MJA0G
16	330	HA0	0.16	0.16	600	EMZL160□RA331MHA0G
	470	HA0	0.16	0.16	600	EMZL160□RA471MHA0G
	680	JA0	0.16	0.08	850	EMZL160□RA681MJA0G
	820	HA0	0.16	0.08	850	EMZL160□RA821MHA0G
	1,300	JA0	0.16	0.06	1,190	EMZL160□RA132MJA0G
25	220	HA0	0.14	0.16	600	EMZL250□RA221MHA0G
	330	HA0	0.14	0.16	600	EMZL250□RA331MHA0G
	470	HA0	0.14	0.08	850	EMZL250□RA471MHA0G
	470	JA0	0.14	0.08	850	EMZL250□RA471MJA0G
	560	HA0	0.14	0.08	850	EMZL250□RA561MHA0G
	820	JA0	0.14	0.06	1,190	EMZL250□RA821MJA0G
35	1,000	JA0	0.14	0.06	1,190	EMZL250□RA102MJA0G
	100	HA0	0.12	0.16	600	EMZL350□RA101MHA0G
	220	HA0	0.12	0.16	600	EMZL350□RA221MHA0G
	330	HA0	0.12	0.08	850	EMZL350□RA331MHA0G
	330	JA0	0.12	0.08	850	EMZL350□RA331MJA0G
	470	HA0	0.12	0.08	850	EMZL350□RA471MHA0G
	560	JA0	0.12	0.06	1,190	EMZL350□RA561MJA0G
50	680	JA0	0.12	0.06	1,190	EMZL350□RA681MJA0G
	100	HA0	0.10	0.34	350	EMZL500□RA101MHA0G
	220	JA0	0.10	0.18	670	EMZL500□RA221MJA0G

□ : Enter the appropriate terminal code.

New products are indicated in red text.

◆RATED RIPPLE CURRENT MULTIPLIERS

●Frequency Multipliers

Capacitance(μF)	Frequency(Hz)			
	120	1k	10k	100k
100	0.40	0.75	0.90	1.00
220 to 560	0.50	0.85	0.94	1.00
680 to 1,500	0.60	0.87	0.95	1.00

The deterioration of aluminum electrolytic capacitors accelerates their life due to the internal heating produced by ripple current. For details, refer to Section "5-3 Ripple Current Effect on Lifetime" in the catalog, Technical Note.



- Always read "Notes on Use" before using the product in order to enable you to use the product correctly and prevent any faults and accidents from occurring.
- Request the Product Specification on the product of NIPPON CHEMI-CON CORPORATION to refer to it as well as this brochure prior to the order of the products. Some specific notes on use of the ordered product may be described in the specifications.
- The products listed in this catalog are designed and manufactured for general electronics equipment use and are not intended for use in applications that can adversely affect human life; where the malfunction of equipment may cause damage to life or property. In addition, our products are not intended to be used in specific applications that may cause a major social impact. Please consult with us in advance of usage of our products in the following listed applications. ① Aerospace equipment ② Power generation equipment such as thermal power, nuclear power etc. ③ Medical equipment ④ Transport equipment (automobiles, trains, ships, etc.) ⑤ Transportation control equipment ⑥ Disaster prevention / crime prevention equipment ⑦ Highly publicized information processing equipment ⑧ Submarine equipment ⑨ Other applications that are not considered general-purpose applications.
- The circuits described as examples in this catalog and the "delivery specifications" are featured in order to show the operations and usage of our products, however, this fact does not guarantee that the circuits are available to function in your equipment systems. We are not in any case responsible for any failures or damage caused by the use of information contained herein. You should examine our products, of which the characteristics are described in the "delivery specifications" and other documents, and determine whether or not our products suit your requirements according to the specifications of your equipment systems. Therefore, you bear final responsibility regarding the use of our products.
Please make sure that you take appropriate safety measures such as use of redundant design and malfunction prevention measures in order to prevent fatal accidents and/or fires in the event any of our products malfunction.
- We strongly recommend our customers to purchase Nippon Chemi-Con products only through our official sales channels. We assume no responsibility for any defects or damages caused by using products purchased from outside our official sales channel or of counterfeit goods. In addition, we will ask the customer to pay the investigation cost for products purchased outside our official sales channel.
- We reserve the right to discontinue production and delivery of products. We do not guarantee that all the products included in this catalog will be available in the future.
The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products
- We continually strive to improve the quality and reliability of our products, but in any case that our product does not meet our published specifications, please stop using it promptly and contact us immediately. As for compensation for non-conforming goods delivered by Chemi-Con, we will limit it only to goods found in non-compliance of our published specifications. This may be accomplished by a no cost replacement of non-conforming individual products, a credit of the piece price paid per each individual non-conforming product, or in other ways deemed necessary.
In addition, we have an established system with enhanced traceability, therefore we will limit the applicable lot items for any potential compensation.

[Part Numbering System](#)

[Part Numbering System \(Appendix\)](#)

[Standardization](#)

[Available Items by Manufacturing Locations](#)

[Environmental Measures](#)

[Technical Note](#)

[Precautions and Guidelines](#)

[Recommended Soldering Conditions](#)

[Taping, Lead-preforming and Packaging](#)

[Available Terminals for Snap-in and Screw Mount Type](#)