



WITH ATTACHMENT



ATTACHMENT OPTIONS:



NOTE1:
CONTACT SALES TEAM
FOR GASKET OPTIONS.

NOTE 2:
DOES NOT APPLY FOR COMPOSITE
(OPTION 74). ACTUAL VALUE FOR
COMPOSITE IS 23,00 ± 0,50

OMIT FOR NO ATTACHMENT
(SEE SHEET 2)

100P237-17-1-C-WR4-17

SERIES _____
INSERT 'F' FOR FLUOROSILICONE GASKET
OMIT FOR STANDARD SILICONE GASKET
SHELL SIZE (TABLE 1) _____
MATERIAL (TABLE 5) _____
FINISH (TABLE 6) _____
LANYARD TYPE (TABLE 4) _____
LANYARD LENGTH (IN INCHES) _____
+1,0"/-0" TOLERANCE
ATTACHMENT (SEE ABOVE) _____

DRAWN	K.SHEPPARD		DATE	10/02/2014	 3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER:				100P237 SERIES				 Polamco 		
SALES APPR	A.POLSON		10/02/2014			TITLE:				PLUG PROTECTION CAP						
DESIGN APPR				UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0.25MM ANGULAR +/- 1°		ASSY USED ON: MIL-DTL-38999 SERIES III PLUG										
PROD APPR																
QUAL APPR					MATERIAL SEE PART NUMBER BREAKDOWN	THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.								POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP	SHT 1	DRAWING NO: P10270
ISSUE 11	REV. 2	DCR 3969		FINISH SEE PART NUMBER BREAKDOWN												
NCAGE CODE U5792			WEIGHT													

TABLE 1

SHELL SIZE	ØA MAX	B THREAD	ØC MIN
09	21,0	0.625-0.1P-0.3L-TS	12,6
11	24,5	0.750-0.1P-0.3L-TS	15,8
13	28,0	0.875-0.1P-0.3L-TS	19,4
15	30,0	1.000-0.1P-0.3L-TS	22,6
17	34,0	1.1875-0.1P-0.3L-TS	25,8
19	37,0	1.250-0.1P-0.3L-TS	28,6
21	40,0	1.375-0.1P-0.3L-TS	31,8
23	43,0	1.500-0.1P-0.3L-TS	34,8
25	47,0	1.625-0.1P-0.3L-TS	38,1

TABLE 2

EYELET REF.	ØF
01	3,2
02	3,7
03	4,3
04	5,3
05	6,4

TABLE 3

RING REF.	SPLIT RING.REF	ØE
09	S09	15,1
11	S11	18,0
13	S13	19,4
15	S15	22,6
17	S17	25,8
19	S19	28,8
21	S21	32,0
23	S23	34,1
25	S25	40,1

TABLE 4

CODE	LANYARD TYPE
WR	NYLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
TC	TEFLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
WG	TEFLON COVERED (OLIVE DRAB) STAINLESS STEEL WIRE ROPE
WB	TEFLON COVERED (BLACK) STAINLESS STEEL WIRE ROPE
WRB	PVC COVERED (BLACK) STAINLESS STEEL WIRE ROPE
LC	LINK CHAIN
BK	BLACK CORD
VGB	1,5mm BLACK POLYESTER CORD EQV. TO DIN83330-E1,5
B	BEAD CHAIN
R	OLIVE DRAB POLYESTER CORD
NB	OLIVE DRAB NYLON CORD
NK	BLACK NYLON CORD

TABLE 5

CODE	MATERIAL
1	ALUMINIUM
2	NICKEL ALUMINIUM BRONZE
4	STAINLESS STEEL
7	BLACK ACETAL
74	COMPOSITE



LIST NOT EXHAUSTIVE, SEE MATERIAL TABLE FOR OTHER OPTIONS

TABLE 6

CODE	DESCRIPTION
B	CADMIUM, OLIVE DRAB OVER ELECTROLESS NICKEL
C	ELECTROLESS NICKEL
G	BLACK ANODISE, SULPHURIC
J	PASSIVATE
U	UNPLATED CLEAN FINISH NOT SHOT BLASTED
Z	SHOT BLAST FOR NON-REFLECTIVE FINISH
ZB	ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
ZN	ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL

LIST NOT EXHAUSTIVE, SEE PLATING TABLE FOR OTHER OPTIONS

WITHOUT ATTACHMENT

100P237-17-1-C
NO ATTACHMENT VERSION100P237-17-1-C-EO
EYELET ONLY VERSION
(NO LANYARD)

DRAWN	K.SHEPPARD		DATE	10/02/2014			3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER:				 Polamco 		
SALES APPR	A.POLSON		DATE	10/02/2014				100P237 SERIES						
DESIGN APPR						UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0.25MM ANGULAR +/- 1°	TITLE:	PLUG PROTECTION CAP						
PROD APPR														
QUAL APPR								MATERIAL	ASSY USED ON: MIL-DTL-38999 SERIES III PLUG					
ISSUE	REV.	DCR				FINISH	SEE PART NUMBER BREAKDOWN	THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.				POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP	SHT 2	DRAWING NO: P10270
11	2	3969												
NCAGE CODE U5792			WEIGHT		SEE PART NUMBER BREAKDOWN									