
CUI Devices is now Same Sky! Learn More

MODEL: CMM-3424DT-26165-TR | DESCRIPTION: MEMS MICROPHONE

FEATURES

- IP67 rated
- top port
- digital
- omnidirectional



ELECTRICAL

parameter	conditions/description	min	typ	max	units
directivity	omnidirectional				
sensitivity (S)[1]	at 94 dB SPL, 1 kHz	-27	-26	-25	dB FS
supply voltage (V_{DD})[1]		1.6		3.6	V
current consumption (I_{DD})[1, 6]	standard mode low-power mode	600	800 300	1,000 400	µA µA
stanby current (ISTANDBY)[5, 6]	F_{CLOCK} < 250 kHz		10	30	µA
signal to noise ratio (S/N)	at 94 dB SPL, 1 kHz (A-weighted)		65		dBA
total harmonic distortion (THD)	at 94 dB SPL, 1 kHz at 120 dB SPL, 1 kHz		0.15	0.3 10	% %
acoustic overload point (AOP)	at 10% THD, 1 kHz		120		dB SPL
power supply rejection ratio (PSSR) (standard mode)	200 mVp-p sine wave @ 1 kHz VDD=1.8 V VDD=3.3 V		 65 65		 dB dB
power supply rejection ratio (PSSR) (low-power mode)	200 mVp-p sine wave @ 1 kHz VDD=1.8 V VDD=3.3 V		 72 72		 dB dB
power supply rejection (PSR) (standard mode)	100 mVp-p square wave @ 217 Hz VDD=1.8 V VDD=3.3 V		 -80 -80		 dB FS dB FS
power supply rejection (PSR) (low-power mode)	100 mVp-p square wave @ 217 Hz VDD=1.8 V VDD=3.3 V		 -90 -90		 dB FS dB FS
polarity	increasing sound pressure		increasing density of 1's		

Downloaded from Arrow.com.


DIGITAL INTERFACE

parameter	conditions/description	min	typ	max	units
clock frequency	standard mode low-power mode	1 350		4.8 800	MHz kHz
fall-asleep time[2, 3]	F_{CLOCK} < 1 kHz, V_{DD} = On			10	ms
wake-up time[2, 4]	F_{CLOCK} ≥ 1 MHz, V_{DD} = On			10	ms
data format	1/2 cycle PDM				
short circuit output current (I_{SC})	grounded output pin		1	10	mA
output load (C_{LOAD})				500	pF
logic input high (V_{IH})		0.65xV_{DD}			V
logic input low (V_{IL})				0.35xV_{DD}	V
logic output high (V_{OH})	I_{OUT} = 2 mA			V_{DD}+0.3	V
logic output low (V_{OL})	I_{OUT} = 2 mA	-0.3			V
clock duty cycle		40		60	%
clock rise time	t_{cr}			10	ns
clock fall time	t_{ct}			10	ns
delay time for valid data (t_{dv}) CLK=3.072 MHz oscilloscope	data trans high VDD=1.8 V VDD=3.3 V	 30 24		 180 119	 ns ns
	data trans low VDD=1.8 V VDD=3.3 V	 30 22		 180 118	 ns ns
delay time to for high Z (t_{dz}) CLK=3.072 MHz oscilloscope	data trans high VDD=1.8 V VDD=3.3 V	 1 1		 14 10	 ns ns
	data trans low VDD=1.8 V VDD=3.3 V	 1 1		 14 10	 ns ns
settling time (t_s)	VDD=1.8 V VDD=3.3 V		13.5 13.5	25 25	ms ms
startup time	powered down => active mode VDD=1.8 V VDD=3.3 V		 13.5 13.5	 25 25	 ms ms

Notes:
1. 100% tested.
2. Valid microphone states are: Power Down Mode (mic off), Sleep Mode (low current, no output, fast start-up), and Active Mode (normal operation).
3. Time from fclock < 1KHz to sleep current specification is met when transitioning from Active to Sleep Mode.
4. Time from fclock ≥ 1MHz to all applicable specifications when transitioning from Sleep to Active Mode.
5. ΔIDD = 0.5 × VDD × CLOAD × fclock.
6. Specified max values are measured at VDD = +3.6V
7. All specifications measured at 15~25°C, humidity at 60~70%, V_{DD} = 1.8 V, F_{CLOCK} = 3.072 MHz (768 kHz in low-power mode), no load, unless otherwise noted.


Downloaded from Arrow.com.

TIMING CHARACTERISTICS



Label	Select	Drives Data After	High-Z After
Data_H	High	rising clock edge	falling clock edge
Data_L	Low(default)	falling clock edge	rising clock edge

RECOMMENDED INTERFACE CIRCUIT



Downloaded from Arrow.com.

ENVIRONMENTAL

parameter	conditions/description	min	typ	max	units
operating temperature		-40		125	°C
storage temperature	in packaging	-40		125	°C
RoHS	yes				
IP level	IP67				


MECHANICAL

parameter	conditions/description	min	typ	max	units
dimensions	4.00 x 3.00 x 1.15				mm
acoustic port	top				
terminals	surface mount				
weight				0.03	g

MECHANICAL DRAWING

units: mm
tolerance: ±0.10 mm


TERMINAL CONNECTIONS	
TERM.	FUNCTION
1	VDD
2	select
3	CLOCK
4	DATA
5	GND
6	GND
7	GND
8	GND




Recommended PCB Layout
Top View

Downloaded from Arrow.com.

FREQUENCY RESPONSE CURVE



MICROPHONE STATE DIAGRAM




Downloaded from Arrow.com.

SOLDERABILITY


parameter	conditions/description	min	typ	max	units
reflow soldering[8]	see reflow profile			260	°C

Note: 8. Not recommended to exceed 3 reflow cycles.



HANDLING RECOMMENDATIONS

1. Not recommended to blow air heavily over acoustic port as debris could impact mic function.
2. Not suitable for wash process after reflow.
3. Not recommended to brush board with or without solvents after reflow process.
4. Not recommended to directly expose to ultrasonic processing or cleaning.
5. Not recommended to inserty any object in port of device at any time.
6. Not recommended to apply over 30 psi of air pressure into the port hole.
7. Not recommended to pull a vacuum over port hole.
8. Not recommended to apply a vacuum when repackaging into sealed bag a rate faster than 0.5 atm/sec.
9. Not recommended to clean table or carried plate with air guarding system that could induce particle floating inside mic.




Recommended Vacuum Nozzle Pickup
Top View


Downloaded from Arrow.com.

PACKAGING

parameter	conditions/description	min	typ	max	units
MSL	Class 1				
reel size	Ø330 mm				
reel QTY	5,200 pcs per reel				
carton size	350 x 175 x 355 mm				
carton QTY	26,000 pcs				



Item	W	E	F	ØDO	D1	Ao	Ko
DIM(mm)	12.0±0.30	1.75±0.10	5.50±0.10	1.55±0.05	1.50 (min)	4.30±0.10	1.30±0.10
Item	PO	10PO	P1	P2	T	Bo	--
DIM(mm)	4.0±0.10	40.0±0.10	8.0±0.10	1.0±0.10	0.30±0.05	3.20±0.10	--



Downloaded from Arrow.com.

REVISION HISTORY

rev.	description	date
1.0	initial release	05/17/2023
1.01	CUI Devices rebranded to Same Sky	09/11/2024
1.02	modified chip design circuit	02/27/2025

The revision history provided is for informational purposes only and is believed to be accurate.

Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

sameskydevices.com

Downloaded from Arrow.com.