



Slip Ring with Flange - 22mm diameter, 6 wires, max 240V @ 2A

PRODUCT ID: 736

IN STOCK

1	ADD TO CART
---	-------------

1-9

10-99

100+

ADD TO WISHLIST

DESCRIPTION

TECHNICAL DETAILS



DESCRIPTION

With a slip ring assembly, your electronics can now twist and turn safely. Add wheel encoders, 360 degree sensors, rotating LEDs, rotors and more! We've seen a lot of people DIY slip ring's out of desperation but no longer, simply pick up one of these to solve any rotation needs you have.

Inside the plastic tube is a gold plated slip ring for 6 wires. There are six color coded wire sets made of 26 AWG and no matter how you twist the assembly, they will remain in continuity. Each of the wire sets can carry up to 2A at up to 240VAC or 240VDC. There's a 44mm (1.7") diameter flange with mounting holes to make it easy to attach or you can cut it off with a hacksaw and drill/machine as you wish it seems to just be ABS plastic. Rated to rotate up to 300 RPM (but you can probably go faster if you don't mind a reduced life and/or noise).

Note: Wire colors may vary.



TECHNICAL DETAILS

- Rated voltage: 240VAC/240VDC
- Rated current: 2 Amp
- 6 x 6" long 26 AWG wires

[Check out the datasheet for the SRC022A-6 for all specifications](#)



MAY WE ALSO SUGGEST...



Miniature Slip Ring - 12mm



Small Reduction Stepper



Miniature Slip Ring - 12mm



Stepper motor - NEMA-17



Slip Ring with Flange -



Small Reduction Stepper

DISTRIBUTORS [EXPAND TO SEE DISTRIBUTORS](#)

[CONTACT](#)

[SUPPORT](#)

[DISTRIBUTORS](#)

[EDUCATORS](#)

[JOBS](#)

[FAQ](#)

[SHIPPING & RETURNS](#)

[TERMS OF SERVICE](#)

[PRIVACY & LEGAL](#)

[ABOUT US](#)

ENGINEERED IN NYC [Adafruit](#)®

"Collaborative production is simple: no one person can take credit for what gets created, and the project could not come into being without the participation of many"
- [Clay Shirky](#)



4.9 ★★★★★
Google
Customer Reviews