

MOSFET – Small Signal, Single P-Channel, XLLGA3 -30 V, -130 mA

NTNS41006PZ

Features

- Single P-Channel MOSFET
- Ultra Small and Thin Package (0.62 x 0.62 x 0.4 mm)
- Low $R_{DS(on)}$ Solution in 0.62 x 0.62 mm Package
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Applications

- Small Signal Load Switch
- Analog Switch
- High Speed Interfacing
- Optimized for Power Management in Ultra Portable Products

MAXIMUM RATINGS ($T_J = 25^\circ\text{C}$ unless otherwise stated)

Parameter		Symbol	Value	Units
Drain-to-Source Voltage		V_{DSS}	-30	V
Gate-to-Source Voltage		V_{GS}	± 20	V
Continuous Drain Current (Note 1)	Steady State	$T_A = 25^\circ\text{C}$	I_D	mA
		$T_A = 85^\circ\text{C}$	-99	
	$t \leq 5\text{ s}$	$T_A = 25^\circ\text{C}$	-148	
Power Dissipation (Note 1)	Steady State	$T_A = 25^\circ\text{C}$	P_D	mW
	$t \leq 5\text{ s}$	$T_A = 25^\circ\text{C}$	121	
Pulsed Drain Current		$t_p = 10\text{ }\mu\text{s}$	I_{DM}	140
Operating Junction and Storage Temperature		T_J, T_{STG}	-55 to 150	$^\circ\text{C}$
Source Current (Body Diode)		I_S	-137	mA
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)		T_L	260	$^\circ\text{C}$

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE RATINGS

Parameter	Symbol	Max	Units
Junction-to-Ambient – Steady State (Note 1)	$R_{\theta JA}$	1035	$^\circ\text{C/W}$
Junction-to-Ambient – $t \leq 5\text{ s}$ (Note 1)	$R_{\theta JA}$	895	

1. Surface Mounted on FR4 Board using the minimum recommended pad size, (or 2 mm^2), 1 oz Cu.
2. Pulse Test: pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.




ON Semiconductor®

www.onsemi.com

MOSFET

$V_{(BR)DSS}$	$R_{DS(on)}$ MAX	I_D MAX
-30 V	4.0 Ω @ -10 V	
	7.0 Ω @ -4.5 V	-130 mA

P-Channel MOSFET



MARKING DIAGRAM



J = Specific Device Code

M = Date Code

ORDERING INFORMATION

Device	Package	Shipping [†]
NTNS41006PZTCG	XLLGA3 (Pb-Free)	8000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

NTNS41006PZ

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition	Min	Typ	Max	Units
-----------	--------	----------------	-----	-----	-----	-------

OFF CHARACTERISTICS

Drain-to-Source Breakdown Voltage	$V_{(\text{BR})\text{DSS}}$	$V_{\text{GS}} = 0 \text{ V}, I_D = -250 \mu\text{A}$	-30			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$V_{(\text{BR})\text{DSS}/T_J}$	$I_D = -250 \mu\text{A}$, ref to 25°C		32		$\text{mV}/^\circ\text{C}$
Zero Gate Voltage Drain Current	I_{DSS}	$V_{\text{GS}} = 0 \text{ V}, V_{\text{DS}} = -24 \text{ V}$		-1.0		μA
Gate-to-Source Leakage Current	I_{GSS}	$V_{\text{DS}} = 0 \text{ V}, V_{\text{GS}} = \pm 12 \text{ V}$		± 2.0		μA

ON CHARACTERISTICS (Note 3)

Gate Threshold Voltage	$V_{\text{GS}(\text{TH})}$	$V_{\text{GS}} = V_{\text{DS}}, I_D = -250 \mu\text{A}$	-1.0		-3.0	V
Negative Threshold Temperature Coefficient	$V_{\text{GS}(\text{TH})/T_J}$			4.0		$\text{mV}/^\circ\text{C}$
Drain-to-Source On Resistance	$R_{\text{DS}(\text{on})}$	$V_{\text{GS}} = -10 \text{ V}, I_D = -100 \text{ mA}$		2.1	4.0	Ω
		$V_{\text{GS}} = -4.5 \text{ V}, I_D = -50 \text{ mA}$		3.3	7.0	
Forward Transconductance	g_{FS}	$V_{\text{DS}} = -5 \text{ V}, I_D = -50 \text{ mA}$		0.14		S
Source-Drain Diode Voltage	V_{SD}	$V_{\text{GS}} = 0 \text{ V}, I_S = -50 \text{ mA}$		-0.8	-1.0	V

CHARGES & CAPACITANCES

Input Capacitance	C_{ISS}	$V_{\text{GS}} = 0 \text{ V}, f = 10 \text{ kHz}, V_{\text{DS}} = -15 \text{ V}$		9.1		pF
Output Capacitance	C_{OSS}			3.2		
Reverse Transfer Capacitance	C_{RSS}			1.9		
Total Gate Charge	$Q_{\text{G}(\text{TOT})}$	$V_{\text{GS}} = -10 \text{ V}, V_{\text{DS}} = -15 \text{ V}, I_D = -100 \text{ mA}$		1.4		nC
Total Gate Charge	$Q_{\text{G}(\text{TOT})}$			0.7		
Threshold Gate Charge	$Q_{\text{G}(\text{TH})}$			0.3		
Gate-to-Source Charge	Q_{GS}			0.4		
Gate-to-Drain Charge	Q_{GD}			0.1		

SWITCHING CHARACTERISTICS, $V_{\text{GS}} = -10 \text{ V}$ (Note 3)

Turn-On Delay Time	$t_{\text{d}(\text{ON})}$	$V_{\text{GS}} = -10 \text{ V}, V_{\text{DD}} = -15 \text{ V}, I_D = -100 \text{ mA}, R_{\text{G}} = 2 \Omega$		22.5		ns
Rise Time	t_r			33.1		
Turn-Off Delay Time	$t_{\text{d}(\text{OFF})}$			178.9		
Fall Time	t_f			101.3		

SWITCHING CHARACTERISTICS, $V_{\text{GS}} = -4.5 \text{ V}$ (Note 3)

Turn-On Delay Time	$t_{\text{d}(\text{ON})}$	$V_{\text{GS}} = -4.5 \text{ V}, V_{\text{DD}} = -15 \text{ V}, I_D = -100 \text{ mA}, R_{\text{G}} = 2 \Omega$		58.7		ns
Rise Time	t_r			137.3		
Turn-Off Delay Time	$t_{\text{d}(\text{OFF})}$			78.6		
Fall Time	t_f			99.7		

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

3. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate-to-Source Voltage




Figure 4. On-Resistance vs. Drain Current and Gate Voltage




Figure 5. On-Resistance Variation with Temperature









Figure 6. Drain-to-Source Leakage Current vs. Voltage

TYPICAL CHARACTERISTICS



NTNS41006PZ

TYPICAL CHARACTERISTICS




Figure 12. FET Thermal Response




SCALE 8:1

XLLGA3, 0.62x0.62, 0.35P

CASE 713AA

ISSUE D

DATE 12 MAR 2021

GENERIC
MARKING DIAGRAM*


X = Specific Device Code
M = Date Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "■", may or may not be present. Some products may not follow the Generic Marking.

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	0.34	0.39	0.43
A1	0.000	---	0.03
b	0.10	0.15	0.20
D	0.57	0.62	0.67
D2	0.175	BSC	
D3	0.205	BSC	
E	0.57	0.62	0.67
E2	0.40	0.50	0.60
e	0.350	BSC	
k	0.200	REF	
L	0.09	0.15	0.21
L2	0.11	0.21	0.31

RECOMMENDED
MOUNTING FOOTPRINT

* For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

DOCUMENT NUMBER:	98AON67527E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	XLLGA3, 0.62x0.62, 0.35P	PAGE 1 OF 1

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **ONSEMI**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales

