


Data Sheet | Item Number: 289-551


Interface module; with solder pin; Female connector; 15-pole; for mating connectors with IDC; Vertical mounting; PCB terminal blocks, double-row; in mounting carrier; 2,50 mm²



<https://www.wago.com/289-551>



Similar to illustration



Electrical data

Operating voltage	≤ 125 VAC/VDC
Nominal current	2 A
Contact resistance (max.)	30 mΩ

Safety and protection

Rated Voltage	125 V
Rated impulse withstand voltage	0.8 kV
Pollution degree	2
Protection type	IP20
Insulation type	Basic insulation

Connection data

Performance level	2 / 200 mating cycles
Strain relief	UNC 4-40 stud bolt
Connection 1	
Pluggable connector	D-subminiature female connector
Pole number 1	15
Connection type	System
Note (conductor cross-section)	12 AWG: THHN, THWN
Mating direction	vertical



Connection 2	
Design	PCB terminal blocks (double-row)
Pole number	15
Connection type	Field
Connection technology	CAGE CLAMP®
WAGO connector	WAGO 236 Series
Solid conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Fine-stranded conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Strip length	5 ... 6 mm / 0.2 ... 0.24 inches

Physical data		
Width	46 mm / 1.811 inches	
Height	85 mm / 3.346 inches	
Depth from upper-edge of DIN-rail	34 mm / 1.339 inches	

Mechanical data		
Mounting type	DIN-35 rail	
Housing design	Mounting carrier	

Material data		
Contact material (connector)	Au over Ni	
Fire load	0.668 MJ	
Weight	59.1 g	

Environmental requirements		
Ambient temperature (operation)	-20 ... +50 °C	
Ambient temperature (storage)	-40 ... +70 °C	
Relative humidity	≤ 85 % (non-condensing)	

Standards and specifications		
Standards/specifications	EN 61010-2-201	

Commercial data		
Product Group	6 (INTERFACE ELECTRONIC)	
PU (SPU)	8 (1) pcs	
Packaging type	Box	
Country of origin	DE	
GTIN	4045454417840	
Customs tariff number	85366990990	



Product Classification	
UNSPSC	39121421
eCl@ss 10.0	27-14-11-52
eCl@ss 9.0	27-14-11-52
ETIM 9.0	EC002780
ETIM 8.0	EC002780
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Approvals / Certificates		
General approvals		Declarations of conformity and manufacturer's declarations
		
Approval	Standard	Certificate Name
cURus Underwriters Laboratories Inc.	UL 508	E175199 Vol.2 Sec.1
EAC GZO Almaty Standart	TP TC 004/2011	EAC CoC 03084
Approval	Standard	Certificate Name
EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-
UK-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-

Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 289-551	

Documentation			
Bid Text		Instruction Leaflet	
289-551	19.02.2019	xml 3.57 KB	
289-551	06.02.2015	doc 27.00 KB	
		Operation and Assemb- ly Instructions Interface	V 1.0.0 02.04.2025
		pdf 1246.19 KB	

CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 289-551	EPLAN Data Portal 289-551
	
	WSCAD Universe 289-551
	
	ZUKEN Portal 289-551
	

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marking strip



Item No.: 709-196
Marking strips; for laser printer; translucent



Item No.: 709-177
Marking strips; on reel; 7.5 mm wide; not stretchable; plain; snap-on type; translucent



Item No.: 709-178
Marking strips; on reel; 7.5 mm wide; not stretchable; plain; snap-on type; white

1.1.2 Tool


1.1.2.1 Operating tool




Item No.: 210-720
Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured

Installation Notes

Conductor termination




Conductor termination – screwdriver actuation parallel to conductor entry




Conductor termination – screwdriver actuation perpendicular to conductor entry

Installation



Snapping a module onto DIN-rail.



Removing a module from the DIN-rail.