







△ MARKING: HTK
(REVERSE SIDE)

DATE CODE
(REVERSE SIDE)



NOTE 1. CONTACT PLATING
GOLD (0.2 μ m MIN.) ON MATING AREA,
GOLD (0.05 μ m MIN.) ON TERMINATION AREA,
ALL OVER NICKEL UNDERPLATED.

2. SUITABLE CABLE
: AWG#20 MAX.



PCS-E68FS+	68	52.1	1.27x (34-1) =41.91	45.88	1, 34, 35, 68
PCS-E50FS+	50	40.7	1.27x (25-1) =30.48	34.45	1, 25, 26, 50
PCS-E36FS+	36	31.8	1.27x (18-1) =21.59	25.56	1, 18, 19, 36
PCS-E28FS+	28	26.7	1.27x (14-1) =16.51	20.48	1, 14, 15, 28
PCS-E20FS+	20	21.65	1.27x (10-1) =11.43	15.4	1, 10, 11, 20
PART NO.	NO. OF POS.	A	B	C	POS. NO.
DIMENSIONS					MARKING

				4	SPACER	PBT (GF)	2	————	UL94V-0 BLACK	
				3	CONTACT	PHOSPHOR BRONZE	NO. OF POS.	NOTE # 1	————	
				2	SHELL	STEEL	1	Ni PLATING	————	
	NOV. 1 2013	A. T	CHANGE MARKING	1	INSULATOR	PBT (GF)	1	————	UL94V-0 BLACK	
LTR.	DATE	BY	REV.	DESCRIPT	No.	PART NAME	MATERIAL	QTY	FINISH	NOTE
DATE MAR. 31. 2004		SCALE 2 / 1		UNIT mm (INCH)	HTK HONDA TSUSHIN KOGYO CO., LTD.					
APP. DATE&REV.										
DR.	DE.	CHK.	CHK.	APP.	NAME		PCS-E TYPE FEMALE CONNECTOR (R0HS)			
A. TASHIRO	A. TASHIRO	K. TASHIRO	S. WATANABE	Y. KATO	PART NO.		PCS-E () FS+ REV. 1 A			