




PRODUCT NUMBER

PITCH

TSxxA1xB00J0G

7.50 mm



Material

- Item(a)Top body:Thermoplastic (UL94V-0)
- Item(b)Bottom body:Thermoplastic (UL94V-0)
- Item(c)Terminal screw:Steel Zinc plating "- " slot type
- Item(d)Clamp:Brass, Ni plated
- Item(e)Female contact:PhBz (CuSn) Tin plated

Electrical cULus/TUV

- Voltage rating: 300VAC/750VAC
- Current rating: 15A/15A
- Wire range:0.2-2.5mm²
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 3.5 Lb-In 0.4Nm
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus TUV

Dim A=(N-1)×7.5+5.6

Dim B=(N-1)×7.5

Dim C=(N-1)×7.5

N=Number of poles

POLES	Tolerance
2p-6p	±0.20
7p-11p	±0.30
12p-16p	±0.40

PART NO.: TS xx A1 x B 00J0 G

Solid block

No. of poles

02 2 poles

03 3 poles

... ..

16 16 poles

Color

0 Black (RAL9005)

2 Red (RAL3001/D)

3 Orange(RAL2011/P)

4 Yellow(RAL1018/A)

5 Green(RAL6018/T)

6 Blue (RAL5015/A)

8 Grey(RAL7035/D)

9 White(RAL1102)

C Green(RAL6018/U)

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family
ltr	ecn	no	dr	date	tolerances unless otherwise specified	MM	TERMINAL BLOCK
					angles	MM	title
					0.1		TERMINAL BLOCK
					X*±1"	scale	PLUGGABLE PLUG,HOOK ON BACK SIDE,WITHOUT FLANGE
					dr EVIN ZHONG 041914		dwg no
					enr EVIN ZHONG 041914		sheet 1 of 1 size
					chr HANKE FENG 041914		TSxxA1xB00J0G A4
					appd SHI JUN 041914		type
							CUSTOMER Drawing
sheet index	revision	A					
	sheet	1					