





PRODUCT NUMBER

PITCH

0QxxB1x000J0G

2.50 mm

RECOMMENDED P.C.B LAYOUT
TOP VIEW

SECTION P-P

Material:

- Item ③ Male contact pin: Copper Tin plated
- Item ④ Terminal housing: Thermoplastic (UL94V-0)

Electrical:

cULus

- Voltage rating: 150V
- Current rating: 4A
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus

Dimension

Dim A	N×2.5+1.9
Dim B	(N-1)×2.5

N=Number of poles

Poles	Tolerance
2p-6p	±0.10
7p-12p	±0.15
13p-18p	±0.20
19p-24p	±0.30

0Q xx B 1 x 0 00J0 G

No. OF POLES
02: 2 POLES
...
24: 24 POLES

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- 9 White(RAL1102)
- C Green(RAL6018/U)

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family			
ltr	ecn	no	dr	date	tolerances unless otherwise specified	MM	TERMINAL BLOCK			
					angles	MM	title			
					0.05		TERMINAL BLOCK			
					0.1		PLUGGABLE SOCKET, VERTICAL			
					X±0.5		dwg no			
					X.X±0.3		sheet 1 of 1			
					X.XX±0.1		size			
					dr		0QxxB1x000J0G			
					enr		A4			
					chr		type			
					appd		CUSTOMER Drawing			
sheet index	revision sheet	A	1							