




Part Number : [1000570474](#)
Product Description : Temp-Flex High-Performance Flat-Ribbon Cable, 34 Circuits, 1.00mm Pitch, 28 AWG, Silver Plated Copper, UL 20424, 7/36 Stranded Extruded FEP, Blue
Series Number : 100057
Status : Active
Product Category : Specialty Wire and Cable
Engineering Number : F2807S-34-0394-5



Documents & Resources

Drawings

[1000570474_sd.pdf](#)
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Specialty Wire and Cable
Series	100057
Description	Temp-Flex High-Performance Flat-Ribbon Cable, 34 Circuits, 1.00mm Pitch, 28 AWG, Silver Plated Copper, UL 20424, 7/36 Stranded Extruded FEP, Blue
Product Name	Temp-Flex
UPC	191128082136

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	300V AC

Physical

Cable Length	100 ft/spool, 10 ft min length, 2 lengths/spool max
Circuits (Loaded)	34
Color - Cable Jacket	Blue
Insulation	FEP
Material - Outer Jacket	FEP
Material - Plating Mating	Silver
Net Weight	20.362/g
Packaging Type	Spool
Pitch - Mating Interface	1.00mm

Temperature Range - Operating	-55° to +200°C
Wire/Cable Type	7/36 Stranded, High-Performance Flat-Ribbon, UL 20424
Wire Size (AWG)	28

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Molex Picoflex

This document was generated on Sep 23, 2025