


MODEL NO.	PACKAGING
134-1000-023	ONE PCS PER BAG

REV	ECO	DATE
001	ECO-17-0023	12/18/2017
002	ECO-18-0023	08/21/2018



NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL & FINISH:
 - 1.1 BODY & SHELL: PASSIVATED STAINLESS STEEL
 - 1.2 CONTACT PIN : GOLD PLATED BERYLLIUM COPPER
 - 1.3 INSULATOR: ULTEM 1000 AMBER
 - 1.4 GASKET: SILICONE RED
 - 1.5 C RING: BERYLLIUM COPPER
2. ELECTRICAL:
 - 2.1 IMPEDANCE: 50 OHMS
 - 2.2 FREQUENCY RANGE: DC-46.5 GHz
 - 2.3 DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS MIN
 - 2.4 VOLTAGE STANDING WAVE RATIO: DC- 4 GHz: 1.05 MAX
4 - 20 GHz: 1.08 MAX
20 - 46.5GHz: 1.15 MAX
 - 2.5 CONTACT RESISTANCE: CENTER CONTACT: 4 MILLIOHMS MAX
OUTER CONTACT: 2.5 MILLIOHMS MAX
 - 2.6 INSULATION RESISTANCE: 5000 MOHM MIN
3. MECHANICAL:
 - 3.1 ENGAGEMENT/ DISENGAGEMENT FORCE: 0.23 NM MAX
 - 3.2 COUPLING PROOF TORQUE: 1.65NM MIN (1.85MM);1.7NM MIN (2.92MM)
 - 3.3 COUPLING NUT RETENTION FORCE: 267 N MIN
 - 3.4 CONTACT RETENTION: 20 N MIN
 - 3.5 DURABILITY: 500 CYCLES MIN
4. ENVIRONMENT:
 - 4.1 THERMAL SHOCK: MIL-STD-202, METHOD 107, CONDITION B.
 - 4.2 OPERATING TEMPERATURE: -65 TO 165°C
 - 4.3 SHOCK: MIL-STD-202, METHOD 213, CONDITION I
 - 4.4 VIBRATION: MIL-STD-202, METHOD 204, CONDITION D
 - 4.5 MOISTURE RESISTANCE: MIL-STD-202, METHOD 106

Model No. 134-1000-023		Johnson	
RoHS2		File: ADAPTER ASSEMBLY.185mm PLUG TO 2.92mm(SMK) PLUG	
2011/95/EU		Drawing No. 134-1000-023	
XXXX + 02		Rev. 002	
XXXX + 01		Date: 08/21/2018	
ANGLES: 10°		SAC C	
		DO NOT SCALE DRAWING	
		NONE	
		Sheet 1 of 1	