Data sheet

# CLI C 2-4 GE/SW 2 CD

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com




Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

## General ordering data

| | |
|---|---|
| Version | CableLine, Conductor and cable markers, 4 - 10 mm, 4 x 7 mm, yellow |
| Order No. | 1568261508 |
| Type | CLI C 2-4 GE/SW 2 CD |
| GTIN (EAN) | 4008190083540 |
| Qty. | 250 items |



Downloaded from Arrow.com.

# Data sheet

## CLI C 2-4 GE/SW 2 CD

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 8 mm | Depth (inches) | 0.315 inch |
| Height | 4 mm | Height (inches) | 0.1575 inch |
| Width | 7 mm | Width (inches) | 0.2756 inch |
| Net weight | 0.21 g | | |

### Temperatures

| | |
|---|---|
| Operating temperature range | -30…80 °C |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

### General data

| | | |
|---|---|---|
| Material colour according to resistance code | 4 | |
| Orientation of print | horizontal | |
| Type of printing | Standard | |
| Printing method | hot-embossing | |
| Version | CD | |
| Width | 7 mm | |
| UL 94 flammability rating | V-0 | |
| Operating temperature range, max. | 80 °C | |
| Operating temperature range, min. | -30 °C | |
| Colour | yellow | |
| Halogen | Yes | |
| Insulation cross-section, max. | 10 | |
| Basic material | PVC, soft, without Cadmium | |
| Colour of printing | black | |
| Printed characters | Numbers | |
| Number of markers per packaging unit | Form of supply | Reel |
| Recommended industries | Process, Machinery | |
| Number of markers per combination | 1 Reel = Conductor and cable markers | |
| Operating temperature range | -30…80 °C | |
| Imprint | 2 | |

### Conductor and cable markers

| | | | |
|---|---|---|---|
| Halogen | Yes | Conductor cross-section, max. | 16 mm² |
| Conductor cross-section, min. | 2.5 mm² | Conductor O.D., max. | 10 mm |
| Conductor O.D., min. | 4 mm | Conductor O.D. | 4 - 10 mm |
| Cross-section for connected wire | 2.5 - 16 mm² | | |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |



Downloaded from Arrow.com.

# CLI C 2-4 GE/SW 2 CD

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings




Similar to illustration



Downloaded from Arrow.com.