


SMD LOW OHMIC – CURRENT SENSE RESISTORS

TYPE RLC73 SERIES

INTRODUCTION

TE Connectivity (TE) introduces a new range of current sense resistors to be offered as a low-cost alternative to legacy solutions characterised by noble metal construction (Ag /Pd / RU) and terminations. RLC73 series has the additional benefit of being fully RoHS compliant, and features power ratings up to 2W and TCRs down to 50ppm/°C in the high-power version. Furthermore, these resistors satisfy the demand for low ohmic shunt resistors to act as current sensors towards ICs for battery charge management and low voltage power supplies produced by global semiconductor manufacturers.



FEATURES

- Resistance values from 10mΩ
- Low TCR version available for many values
- High purity alumina substrate for high power dissipation
- RoHS Compliance
- MSL Level 1

APPLICATIONS

- Power management applications
- Switching power supply
- Over current protection in audio applications
- Voltage regulation module (VRM)
- DC-DC converter
- Battery pack
- Charger
- Adaptor
- Disk driver

CHARACTERISTICS – ELECTRICAL - STANDARD

Type	Size	Power Rating (W)	Operating Temperature Range	Maximum Operating Current (A)	Resistance Range (mΩ)			TCR (PPM/°C)
					±1% E24 & E96*	±2% E24	±5% E24	
RLC73	0805	0.125	-55 ~ 155°C	2.5	20 – 50	20 – 50		±600
					51 – 100	51 – 100		±400
					102 – 196	110 – 180		±300
					200 – 1000	200 – 1000		±200

SMD Low Ohmic – Current Sense Resistors

Type RLC73 Series

CHARACTERISTICS – ELECTRICAL - STANDARD

Type	Size	Power Rating (W)	Operating Temperature Range	Maximum Operating Current (A)	Resistance Range (mΩ)			TCR (PPM/°C)
					±1% E24 & E96*	±2% E24	±5% E24	
RLC73	1206	0.25	-55 ~ 155°C	5.0	10 – 20	10 – 20	±600	
					22 – 50	22 – 50	±400	
					51 – 91	51 – 91	±300	
					100 – 1000	100 – 1000	±200	
RLC73	1210	0.5		7.07	10 – 20	10 – 20	±600	
					22 – 50	22 – 50	±400	
					51 – 91	51 – 91	±300	
					100 – 1000	100 – 1000	±200	
RLC73	2010	0.75		8.66	10 – 20	10 – 20	±600	
					22 – 50	22 – 50	±400	
					51 – 91	51 – 91	±300	
					100 – 1000	100 – 1000	±200	
RLC73	2512	1		10.0	10 – 20	10 – 20	±600	
					22 – 50	22 – 50	±400	
					51 – 91	51 – 91	±300	
					100 – 1000	100 – 1000	±200	

*The nominal resistance value range for less than 100mΩ is in E24 series

CHARACTERISTICS – ELECTRICAL - HIGH POWER

Type	Size	Power Rating (W)	Operating Temperature Range	Maximum Operating Current (A)	Resistance Range (mΩ)			TCR (PPM/C°)
					±1% E24 & E96*	±2% E24	±5% E24	
RLC73P	0805	0.25	-55 ~ 155°C	2.21	20 – 50	20 – 50		±600
					51 – 91	51 – 91		±400
				1.58	100 – 196	100 – 180		±100
					200 – 499	200 – 470		±75
					500 – 1000	500 – 1000		±50

SMD Low Ohmic – Current Sense Resistors


Type RLC73 Series

CHARACTERISTICS - ELECTRICAL - HIGH POWER

Type	Size	Power Rating (W)	Operating Temperature Range	Maximum Operating Current (A)	Resistance Range (mΩ)			TCR (PPM/C°)
					±1% E24 & E96*	±2% E24	±5% E24	
RLC73P	1206	0.5	-55 ~ 155°C	7.07	10 – 20	10 – 20	±600	
					22 – 50	22 – 50	±400	
					51 – 68	51 – 68	±300	
RLC73P	1206	1		3.65	75 – 100	75 – 100	±100	
					102 – 147	110 – 140	±75	
					150 - 1000	150 - 1000	±50	
RLC73P	1210	0.75		8.66	10 – 20	10 – 20	±600	
					22 - 47	22 - 47	±400	
					3.87	50 – 147	50 – 140	±75
150 -1000	150 - 1000	±50						
RLC73P	2010	1		10.0	10 – 20	10 – 20	±600	
					22 - 47	22 - 47	±400	
				4.47	50 – 147	50 – 140	±75	
150 - 1000	150 - 1000	±50						
RLC73P	2512	2		14.1	10 – 18	10 - 18	±600	
				10.0	20 – 47	20 - 47	±100	
				6.32	50 – 147	50 – 140	±75	
					150 - 1000	150 - 1000	±50	

*The nominal resistance value range for less than 100mΩ is in E24 series

CONSTRUCTION AND DIMENSIONS




SMD Low Ohmic – Current Sense Resistors

Type RLC73 Series


Type	Size		L (mm) ±0.10	W (mm)	T (mm)	D1 (mm)	D2 (mm)	Weight (g)
RLC73 / RLC73P	0805		2.00	1.25 ±0.10	0.55 ±0.10	0.30 ±0.20	0.40 ±0.25	4.6
RLC73 / RLC73P	1206		3.10	1.55 ±0.10	0.55 ±0.10	0.50 ±0.30	0.40 ±0.25	8.7
RLC73 / RLC73P	1210		3.10	2.60 ±0.15	0.55 ±0.10	0.50 ±0.30	0.50 ±0.25	16.0
RLC73 / RLC73P	2010		5.00	2.50 ±0.15	0.60 ±0.15	0.60 ±0.30	0.50 ±0.25	23.7
RLC73	2512		6.35	3.10 ±0.15	0.60 ±0.10		0.55 ±0.25	40.0
RLC73P	2512	10-18 mΩ			0.74 ±0.10		2.10 ±0.10	53.6
		20 – 43 mΩ	6.45	3.25 ±0.15	0.85 ±0.10		0.60 ±0.30	65.3
		47 mΩ	6.35	3.10 ±0.15	0.74 ±0.10		210 ±0.10	53.6
		51 – 1000 mΩ						

DERATING CURVE



SOLDERING PROFILE

Soldering Condition (Ref. IPC/JEDEC J-STD-020 & J-STD-002)



Profile Feature	Pb-Free Assembly
Preheat	
Min. Temperature (T _{min})	150 °C
Max Temperature (T _{max})	200 °C
Preheating time (t _s) from (T _{min} to T _{max})	60-120 seconds
Ramp-up rate (T _L to T _p)	3°C/second max.
Liquidous temperature (T _L)	217 °C
Time (t _L) maintained above T _L	60-150 seconds
Min. Peak temperature (T _p min)	235°C
Max. Peak temperature (T _p max)	260°C
Time (t _p) within 5 °C of the specified classification temperature (T _c)	30 seconds max.
Ramp-down rate (T _p to T _L)	6°C/second max.
Time 25 °C to peak temperature	8 minutes max.

SMD Low Ohmic – Current Sense Resistors

Type RLC73 Series

ENVIRONMENTAL CHARACTERISTICS

Item	Requirement	Test Method
Temperature Coefficient of resistance (T.C.R.)	As Spec.	JIS-C-5201-1 4.8 IEC-60115-1 4.8 At 25°C/-55°C and 25°C/+125°C, 25°C is the reference temperature Low TCR: At 25°C/+125°C, 25°C is the reference temperature
Short Time Overload	$\pm(0.5\%+0.05\Omega)$	JIS C 5201-1 4.13 IEC 60115-1 4.13 RCWV*2.5 or Max. Overload Voltage whichever is lower for 5 seconds
	$\pm(1.0\%+0.05\Omega)$ For $\leq 50\text{m}\Omega$ & all High power	
Insulation Resistance	$\geq 10\text{G}$	JIS-C-5201-1 4.6 IEC-60115-1 4.6 Max. Overload Voltage for 1 minute
Endurance	$\pm(1.0\%+0.05\Omega)$	JIS-C-5201-1 4.25 IEC-60115-1 4.25.1 70 $\pm$ 2°C, RCWV for 1000 hrs with 1.5 hrs "ON" and 0.5 hr "OFF"
	$\pm(2.0\%+0.05\Omega)$ For $\leq 50\text{m}\Omega$ & all High power	
Damp Heat with Load	$\pm(0.5\%+0.05\Omega)$	JIS-C-5201-1 4.24 IEC-60115-1 4.24 40 $\pm$ 2°C, 90-95% R.H., RCWV for 1000 hrs with 1.5 hrs "ON" and 0.5 hr "OFF"
	$\pm(1.0\%+0.05\Omega)$ For $\leq 50\text{m}\Omega$ & all High power	
Dry Heat	$\pm(1.0\%+0.05\Omega)$	JIS-C-5201-1 4.23 IEC-60115-1 4.23.2 at +155°C for 1000 hrs
	$\pm(2.0\%+0.05\Omega)$ For $\leq 50\text{m}\Omega$ & all High power	
Bending Strength	$\pm(1.0\%+0.05\Omega)$	JIS-C-5201-1 4.33 IEC-60115-1 4.33 Bending once for 60 seconds with 3mm 2010, 2512 sizes: 2mm
Solderability	95% min. coverage	JIS-C-5201-1 4.17 IEC-60115-1 4.17 245 $\pm$ 5°C for 3 seconds
Resistance to Soldering Heat	$\pm(0.5\%+0.05\Omega)$	JIS-C-5201-1 4.18 IEC-60115-1 4.18 260 $\pm$ 5°C for 10 seconds
Voltage Proof	No breakdown or flashover	JIS-C-5201-1 4.7 IEC-60115-1 4.7 1.42 times Max. Operating Voltage for 1 minute CSN05:300V CSN06/13/10:400V; CSN12:500V
Leaching	Individual leaching area $\leq 5\%$ Total leaching area $\leq 10\%$	JIS-C-5201-1 4.18 IEC-60068-2-58 8.2.1 260 $\pm$ 5°C for 30 seconds
Rapid Change of Temperature	$\pm(0.5\%+0.05\Omega)$	JIS-C-5201-1 4.19 IEC-60115-1 4.19 -55°C to +155°C, 5 cycles

RCWV(Rated Continuous Working Voltage)= $\sqrt{P \cdot R}$ or Max. Operating Voltage whichever is lower.

Storage Temperature: 15~28°C; Humidity < 80%RH


Shelf Life: 2 years from production date

SMD Low Ohmic – Current Sense Resistors

Type RLC73 Series


PACKAGING

Reel Dimensions (mm)



Size	Type	Qty	Tape Width	Reel Diameter	ϕA (mm)	ϕB (mm)	ϕC (mm)	W (mm)	T (mm)
0805	Paper	5K / 1K	8mm	7 inch	178.5 $\pm$ 1.5	60 +0/-1	13.0 $\pm$ 0.2	9.0 $\pm$ 0.5	12.5 $\pm$ 0.5
1206									
1210									
2010	Embossed	4K / 1K	12mm	7 inch	178.5 $\pm$ 1.5	60 +0/-1	13.0 $\pm$ 0.5	13.0 $\pm$ 0.5	15.5 $\pm$ 0.5
2512									
2512 2W	Embossed	2K/ 1K	12mm	7 inch	178.5 $\pm$ 1.5	60 +0/-1	13.0 $\pm$ 0.5	13.0 $\pm$ 0.5	15.5 $\pm$ 0.5

PAPER TAPE SPECIFICATIONS




Size	A (mm) ± 0.10	B (mm) ± 0.20	W (mm) ± 0.20	E (mm) ± 0.10	F (mm) ± 0.05	P_0 (mm) ± 0.10	P_1 (mm) ± 0.05	P_2 (mm) ± 0.05	ϕD_0 (mm) $+0.1 -0$	T (mm) ± 0.1
0805	1.60	2.40	8.0	1.75	3.50	4.00	4.00	2.00	1.50	0.85
1206	1.90	3.50	8.0	1.75	3.50	4.00	4.00	2.00	1.50	0.85
1210	2.90	3.50	8.0	1.75	3.50	4.00	4.00	2.00	1.50	0.85

SMD Low Ohmic – Current Sense Resistors


Type RLC73 Series

EMBOSSED PLASTIC TAPE SPECIFICATIONS



Size	A (mm)	B (mm)	W (mm)	E (mm)	F (mm)	P ₀ (mm)	P ₁ (mm)	P ₂ (mm)	ϕD_0 (mm)	T (mm)
2010	2.80 ±0.10	5.40 ±0.20	12.0 ±0.30	1.75 ±0.10	5.5 ±0.05	4.00 ±0.05	4.00 ±0.10	2.00 ±0.05	1.50 ±0.10	1.00 ±0.20
2512	3.50 ±0.10	6.70 ±0.10	12.0 ±0.30	1.75 ±0.10	5.5 ±0.05	4.00 ±0.05	4.00 ±0.10	2.00 ±0.05	1.50 ±0.10	1.00 ±0.20
2512 2W 20 -49mΩ	3.50 ±0.10	6.70 ±0.10	12.0 ±0.30	1.75 ±0.10	5.5 ±0.05	4.00 ±0.10	4.00 ±0.10	2.00 ±0.05	1.50 ±0.10	1.45 ±0.20
2512 2W 10 - 18mΩ >49mΩ	3.38 ±0.10	6.68 ±0.10	12.0 ±0.30	1.75 ±0.10	5.5 ±0.10	4.00 ±0.10	4.00 ±0.10	2.00 ±0.05	1.55 ±0.05	1.45 ±0.20

RECOMMEND LAND PATTERN



Size	A (mm)	B (mm)	C (mm) ±0.2
0805	1.00	1.00	1.35
1206	2.00	1.15	1.70
1210	2.00	1.15	2.50
2010	3.60	1.40	2.50
2512	4.90	1.60	3.20
2512 2W 20 - 43mΩ	4.90	1.60	3.20
2512 2W 10 - 18mΩ ≥47mΩ	1.00	3.55	3.20


MARKING

4 digit marking for all models

Example

Resistance	10mΩ	51mΩ	100mΩ	549mΩ
Marking	R010	R051	R100	R549

ORDERING INFORMATION



te.com

©2024 TE Connectivity Ltd. Family of Companies. All Rights Reserved.

ALCOWITCH, TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks owned or licensed by the TE Connectivity family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity assumes only those obligations set forth in the terms and conditions for this product and shall in no event be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

02/24 1773269-3 Rev:E ED

INDUSTRIAL / TYPE RLC73 SERIES

