




**Part Number :** [395265002](#)  
**Product Description :** 5.00mm Pitch Eurostyle  
Right-Angle PCB Header, with Threaded  
Retention Inserts, Green Housing, 2 Circuits  
**Series Number :** 39526  
**Status :** Active  
**Product Category :** Terminal Blocks and  
Barrier Strip



## Documents & Resources


**Drawings**  
[395265002\\_sd.pdf](#)

**3D Models and Design Files**  
[395265002\\_stp.zip](#)

**Specifications**  
[PS-39500-001-001.pdf](#)

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant  |
| China RoHS         |  |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Contains Lead per D(2022)9120-DC (17 Jan 2023)  |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863   |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

|                |   |
|----------------|---|
| Status         | Active  |
| Category       | Terminal Blocks and Barrier Strip   |
| Series         | 39526   |
| Description    | 5.00mm Pitch Eurostyle Right-Angle PCB Header, with Threaded Retention Inserts, Green Housing, 2 Circuits |
| Application    | Wire-to-Board   |
| Component Type | PCB Header  |
| Product Name   | Eurostyle Pluggable   |
| Type           | PCB Terminal Blocks and Connectors  |
| UPC            | 822350512992  |

#### Agency

|    |        |
|----|--------|
| UL | E48521 |
|----|--------|

#### Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 15.0A |
| Voltage - Maximum             | 300V  |

#### Physical

|                     |            |
|---------------------|------------|
| Circuits (Loaded)   | 2          |
| Circuits (maximum)  | 2          |
| Color - Resin       | Green      |
| Entry Angle         | N/A        |
| Lock to Mating Part | Yes        |
| Number of Rows      | 1          |
| Orientation         | Horizontal |

|                               |                |
|-------------------------------|----------------|
| Panel Mount                   | No             |
| PC Tail Length                | 3.90mm         |
| PCB Thickness - Recommended   | 3.20mm         |
| Pitch - Mating Interface      | 5.00mm         |
| Pitch - Termination Interface | 5.00mm         |
| Polarized to Mating Part      | Yes            |
| Shrouded                      | Closed Ends    |
| Stackable                     | No             |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size (AWG)               | N/A            |

### Solder Process Data

|                              |     |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
|------------------------------|-----|

---

### Mates With / Use With

#### Mates with Part(s)

| Description                             | Part Number                               |
|---|---|
| 5.00mm Pitch Eurostyle Horizontal Plugs | <u>39524</u>                              |
| 5.00mm Pitch Eurostyle Plugs            | <u>39527</u>                              |
| Mates With                              | Most 5.00mm Pitch Industry Standard Plugs |

---

This document was generated on Feb 28, 2025