

COAXIAL CONNECTOR, TNC, 50 Ohm, Straight panel receptacle, jack (female), flange mount
23_TNC-50-0-6/133_N

Properties

- Threaded coupling mechanism improves control over the interface dimensions
- Used under a higher environmental load than BNC
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 11 GHz



Product configuration	
Interface type	Standard
TNC	IEC 60169-17_MIL-STD-348A/313_CECC 22200

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz

Mechanical data	
Weight	0.017 kg
Mating cycles	500
Flange type	square flange / 25.4 X 25.4
Tab style	solder end

Ordering Information Table	
Item number	Item description
22640551	23_TNC-50-0-6/133_NE

COAXIAL CONNECTOR, TNC, 50 Ohm, Straight panel receptacle, jack (female), flange mount

23_TNC-50-0-6/133_N

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P37993 / Date of publication: 01.02.2024 / uncontrolled copy