



PRODUCT NUMBER	PITCH
TTxx01x000J0G	5.00 mm



Section C-C

Material

- Item ① Clamp: Brass(CuZn) Ni plated
- Item ② Terminal screw: Steel Zinc plating "-" slot type
- Item ③ Female contact: PhBz, Au plated.
- Item ④ Terminal(housing): Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
 - Solid wire(AWG): 16-22
 - Stranded wire(AWG): 16-22
- Torque(Lb-In): 1.7
- Screw: M3
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety approval: cULus

N = Number of poles

Dim A=Nx5.0

Dim B=(N-1)x5.0

poles	Dim A	Dim B
2-6p	±0.15	±0.10
7-12p	±0.25	±0.15
13-18p	±0.30	±0.20
19-24p	±0.40	±0.30

PART NO.: TT xx 01 x 0 00J0 G

End Stackable	No. of poles	Body Color	RoHS compliant
0	2	Black (RAL9005)	(lead<4%)
02	3	Red (RAL3001/D)	In copper Alloy
03	4	Orange(RAL2011/P)	
...	5	Yellow(RAL1018/A)	
...	6	Green(RAL6018/T)	
24	7	Blue (RAL5015/A)	
	8	Grey(RAL7035/D)	
	9	White(RAL1102)	
	C	Green(RAL6018/U)	

mat'l. code				surface	tolerance	projection	product family			
				ASME Y14.5	ASME Y14.5		TERMINAL BLOCK			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title			
					angles	X.±0.5	TERMINAL BLOCK			
					flat	X.X±0.3	PLUGGABLE,180D WIRE INLET,END STACKABLE			
					X'±1"	X.XX±0.1	scale			
					dr	EVIN ZHONG 041614	dwg no			
					enrg	EVIN ZHONG 041614	sheet 1 of 1			
					chr	HANKE FENG 041614	TTxx01x000J0G			
					appd	SHI JUN 041614	type			
sheet index				revision	A		CUSTOMER Drawing			
				sheet	1					