Specification Sheet

Part Number: T50R0PPM4



Polypropylene cable ties deliver excellent resistance to chemicals and salts.

Inside serrations provide strong grip on cables and wire bundles.

Easy application either manually or with a tensioning tool.

Bent tail ensures a quick and simple installation.

Article Number	111-04929
Type	T50R
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's polypropylene cable ties offer added resistance to most chemicals. T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Cable Tie, 8" Long, 25lb Tensile Strength, PP, Black, 1000/pkg

Downloaded from Arrow.com.

Global Part Name	T50R-PP-BK
Minimum Tensile Strength (Imperial)	25
Minimum Tensile Strength (Metric)	110
Length L (Imperial)	7.95
Length L (Metric)	202.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.5
Bundle Diameter Min (Metric)	12.7
Bundle Diameter Max (Imperial)	1.75
Bundle Diameter Max (Metric)	44.5
Thickness T (Imperial)	0.05

Downloaded from Arrow.com.

Thickness T (Metric)	1.2
Cable Tie Head Length (Imperial)	0.29
Cable Tie Head Width (Imperial)	0.3
Material	Polypropylene (PP)
Material Shortcut	PP
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +239°F (-40°C to +115°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

Downloaded from Arrow.com.

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.