

# 100 WATTS


## SINGLE/MULTI OUTPUT AC-DC

### FEATURES:

- Compact 3.3" x 5" x 1.5" Size
- 2 Year Warranty
- Universal 85-264V Input
- 1-4 Tightly-Regulated Outputs
- 0-70°C Operating Temperature
- RoHS Compliant
- IEC 60601-1 3<sup>rd</sup> ed. Medical Cert.
- IEC 62368-1 2<sup>nd</sup> ed. Certification
- IEC 60601-1-2 4<sup>th</sup> ed. EMC
- Class B Emissions per EN55011/32
- Optional Power Fail Warning
- Optional Perforated Cover



CHASSIS/COVER



OPEN CHASSIS

### SAFETY SPECIFICATIONS



Underwriters Laboratories  
File E137708/E140259

UL 62368-1:2014, 2<sup>nd</sup> Edition  
CAN/CSA-C22.2 No. 62368-1-14, 2<sup>nd</sup> Edition  
AAMI/ANSI ES60601-1:2005(R) 2012(R)2021  
CAN/CSA-C22.2 No. 60601-1:2014:2022



CB Reports/Certificates (including all  
National and Group Deviations)

IEC 62368-1:2014, 2<sup>nd</sup> Edition  
IEC 60601-1:2005/A1:2012



TUV SUD America

EN 62368-1:2014, 2<sup>nd</sup> Edition  
EN 60601-1:2006/A1:2013



Low Voltage Directive  
RoHS Directive (Recast)

(2014/35/EU of February 2014)  
(2015/863/EU of March 2015)



Electrical Equipment (Safety) Regulations 2016 SI No. 1101

Restriction of the Use of Certain Hazardous Substances in EEE Regulations  
2012 SI No. 3032 + 2019 SI No.492

### MODEL LISTING

#### MODEL NO. OUTPUT 1 OUTPUT 2 OUTPUT 3 OUTPUT 4

SRW-100-4001	+3.3V/10A(17)	+5V/4A	+12V/2A(18)	-12V/1A
SRW-100-4002	+5V/10A(17)	+24V/2A	+12V/2A(18)	-12V/1A
SRW-100-4003	+5V/10A(17)	+24V/2A	+15V/2A(18)	-15V/1A
SRW-100-4004	+5V/10A(17)	-5.2V/4A	+12V/2A(18)	-12V/1A
SRW-100-4005	+5V/10A(17)	-5.2V/4A	+15V/2A(18)	-15V/1A
SRW-100-4006	+5V/10A(17)	+3.4V/4A	+9V/1A	24V/50A
SRW-100-4007	+5V/10A(17)	+15V/3A	+12V/2A	-12V/1A
SRW-100-4008	+5V/10A(17)	+3.3V/4A	+12V/2A	-5V/1A
SRW-100-4009-IT	+3.3V/10A(17)	+5V/4A	+12V/2A	-5V/1A
SRW-100-4010	+5V/5A	+15V/4A	+12V/2A(18)	9V/2.5A
SRW-100-4011	+5V/10A(17)	-15V/2.2A	+15V/2A(18)	12V/1A
SRW-100-4012	+5V/10A(17)	+3.3V/4A	+12V/2A(18)	-12V/1A
SRW-100-3001	+5V/10A(17)	+12V/4A		-12V/1A
SRW-100-3002	+5V/10A(17)	+15V/3A		-15V/1A
SRW-100-3003	+5V/10A(17)	+3.3V/8A		12V/1A
SRW-100-3004	+3.3V/5A	+5.8V/3A		-48V/1A
SRW-100-3005	+15V/5A	-15V/3A		+5V/2A
SRW-100-2001	+12V/5A	-12V/4A		
SRW-100-2002	+15V/5A	-15V/3A		
SRW-100-2003	+12.5V/4A	+16V/2A		
SRW-100-1001	3.3V/20A(19)			
SRW-100-1002	5V/20A			
SRW-100-1003	12V/8.3A			
SRW-100-1004	15V/6.7A			
SRW-100-1005	24V/4.2A			
SRW-100-1006	28V/3.6A			
SRW-100-1007	48V/2.1A			
SRW-100-1008	40V/2.5A			
SRW-100-1009	3.0-3.3V/20A(19)			
SRW-100-1010	48V/2.1A			
SRP-100-4001	+5V/12A(17)	+24V/3A	+12V/2A(18)	-12V/1A
SRP-100-4002	+5V/12A(17)	+24V/3A	+15V/2A(18)	-15V/1A
SRP-100-4003	+5V/12A(17)	-5V/4A	+12V/2A(18)	-12V/1A
SRP-100-4004	+5V/12A(17)	-5V/4A	+15V/2A(18)	-15V/1A
SRP-100-4005	+5V/12A(17)	+12V/3A	+8V/2A	-8V/1A
SRP-100-3001	+5V/12A(17)	+12V/4A		-12V/1A
SRP-100-2001	+5V/12A(17)	+24V/3A		

# SRW/SRP-100

## OUTPUT SPECIFICATIONS

Total Output Power at 50°C <sub>(1)</sub> (See Derating Chart)	70W 85W 100W	Convection Cooled Convection Cooled w/1Sq.ft baseplate <sub>(16)</sub> 200LFM Forced-Air Cooled <sub>(15)</sub>
Output Voltage Centering	Output 1: Output 2: (SRW) (SRP) Output 3: Output 4:	± 0.25% (All outputs at 50% load) ± 0.25% ± 5.0% ± 2.0% ± 4.0%
Output Voltage Adjust Range	Output 1: Output 2:	95 - 105% 85 - 105% (1001, 4001) 95 - 105% (SRW models only)
Load Regulation	Output 1: Output 2: (SRW) (SRP) Output 3: Output 4:	0.5% (10-100% load change) 0.5% (10-100% load change) 5.0% (10-100% load change) 1.0% (10-100% load change) 1.0% (10-100% load change)
Source Regulation	Outputs 1 - 4:	0.5%
Cross Regulation	Output 2: (SRW) (SRP) Output 3: Output 4:	0.2% (Output 1 load varied 50-100%) 5.0% 0.2% 0.2%
Output Noise	Outputs 1 - 4:	1.0%
Turn on Overshoot		None
Transient Response	Outputs 1 - 4	
Voltage Deviation		5.0%
Recovery Time		2mS
Load Change		50% to 100%
Output Overvoltage Protection (optional)	Output 1:	110% to 150%
Output Overpower Protection	Outputs 1 & 2:	110W Min. Outputs cycle on/off, auto recovery
Output Overcurrent Protection	Outputs 3 & 4:	110% Min.
Hold Up Time		10ms min., 100W Output, 120V Input
Start Up Time		1 Second

## INPUT SPECIFICATIONS

Protection Class	I
Source Voltage	85 - 264 Volts AC
Frequency Range	47 - 63 Hz
Source Current	
True RMS	3A at 85V Input
Peak Inrush	30A
Efficiency	0.68-0.84 (varies by model)

## ENVIRONMENTAL SPECIFICATIONS

Ambient Operating	0°C to + 70°C
Temperature Range	Derating: See Power Rating Chart
Ambient Storage Temp. Range	- 40°C to + 85°C
Temperature Coefficient	Outputs 1 - 4: 0.02%/°C
Altitude	3,000m ASL - Operating 12,192m ASL - Storage

## GENERAL SPECIFICATIONS

Means of Protection	
Primary to Secondary	2MOPP (Means of Patient Protection)
Primary to Ground	1MOPP (Means of Patient Protection)
Secondary to Ground	Operational Insulation(Consult factory for 1MOPP)
Dielectric Strength <sub>(8,9)</sub>	
Reinforced Insulation	5656 VDC, Primary to Secondary
Basic Insulation	2121 VDC, Primary to Ground
Operational Insulation	707 VDC, Secondary to Ground
Leakage Current	
Earth Leakage	<500µA NC, <1000µA SFC
Touch Current	<100µA NC, <500µA SFC
Power Fail Signal (optional) <sub>(14)</sub>	Logic low with input power failure 2ms minimum prior to Output 1 dropping 1%
Remote Sense(single Output Models only) <sub>(10)</sub>	250mV compensation of output cable losses
Mean-Time Between Failures	150,000 Hours min., MIL-HDBK-217F, 25° C, GB
Weight	1.00 Lbs. Open Frame 1.05 Lbs. w/Cover

## ORDERING INFORMATION

Consult factory for alternate output configurations.

Consult factory for positive, negative or floating outputs.

Please specify the following optional features when ordering:

CO - Cover I/O - Isolated Outputs

PF - Power Fail TS - Terminal Strip

OVP - Overvoltage Protection WT - Low Temperature Turn On

All specifications are maximum at 25°C/100W unless otherwise stated, may vary by model and are subject to change without notice.



INTEGRATED


POWER DESIGNS

300 Stewart Road ■ Wilkes-Barre, PA 18706 ■ Phone: (570) 824-4666 ■ Fax: (570) 824-4843 ■ Email: [sales@ipdpower.com](mailto:sales@ipdpower.com) ■ Web: [www.ipdpower.com](http://www.ipdpower.com)

## EMC SPECIFICATIONS (IEC 60601-1-2:2014, 4<sup>TH</sup> ed./IEC 61000-6-2:2005)

Electrostatic Discharge	EN 61000-4-2	±8KV contact / ±15KV air discharge	A
Radiated Electromagnetic Field	EN 61000-4-3	80MHz-2.7GHz, 10V/m, 80% AM	A
Electrical Fast Transients/Bursts	EN 61000-4-4	±2 KV, 5KHz/100KHz	A
Surge Immunity	EN 61000-4-5	±2 KV line to earth / ±1 KV line to line	A
Conducted Immunity	EN 61000-4-6	0.15 to 80MHz, 10V, 80% AM	A
Magnetic Field Immunity	EN 61000-4-8	30A/m, 60 Hz.	A
Voltage Dips	EN 61000-4-11	0% U <sub>T</sub> , 0.5 cycles, 0-315° 100/240V A/A 0% U <sub>T</sub> , 1 cycles, 0° 100/240V A/A 40% U <sub>T</sub> , 10/12 cycles, 0° 100/240V B/A 70% U <sub>T</sub> , 25/30 cycles, 0° 100/240V B/A	
Voltage Interruptions	EN 61000-4-11	0% U <sub>T</sub> , 300 cycles, 0° 100/240V B/B	
Radiated Emissions	EN 55011/32	Class B	
Conducted Emissions	EN 55011/32	Class B	
Voltage Fluctuations/Flicker	EN 61000-3-3	Compliant	


## SRW/SRP-100 SERIES MECHANICAL SPECIFICATIONS



## APPLICATIONS INFORMATION

- Each output can deliver its rated current but Total Output Power must not exceed 70, 85 or 100W, as determined by the cooling method.
- Generally, adequate cooling is provided when semiconductor case temperatures do not exceed 70°C rise and transformer temperature does not exceed 60°C rise at any specified ambient temperature.
- Sufficient area must be provided around power supply to allow natural movement of air to develop in convection-cooled applications.
- This product is intended for use as a professionally-installed component within information technology, industrial, and medical equipment and is not intended for stand-alone operation.
- A minimum load of 10% is required on Output 1 to ensure proper regulation of remaining outputs.
- This product includes only one fuse in the input circuit. In consideration of Clause 8.11.5 of IEC 60601-1:2005, a second fuse may be required in neutral conductor of the end product.
- Peak-to-Peak Output Ripple and Noise is measured directly at the output terminals of the power supply, without the use of the probe ground lead or retractable tip (tip-and-barrel method), 20 MHz bandwidth.
- This product was type-tested and safety-certified using the dielectric strength test voltages listed in Table 6 of IEC 60601-1:2005. In consideration of Clause 8.8.3, care must be taken to ensure that the voltage applied to a reinforced insulation does not overstress different types and levels of insulation. Primary and secondary-to-ground capacitors may need to be disconnected prior to performing a dielectric strength test on the power supply or the end product. It is highly recommended that the DC test voltages listed in DVB.1, Annex DVB of UL 60601-1 1<sup>st</sup> Edition are not exceeded during a production-line dielectric strength test of the assembled end product. Please consult factory for further information.
- This power supply has been safety-approved and final-tested using a DC dielectric strength test. Please consult factory before performing an AC dielectric strength test. Remote-Sense terminals may be used to compensate for cable losses up to 250mV, depending on model. The use of a twisted pair, decoupling capacitors and an appropriately-rated low-impedance capacitor connected across the load will increase noise immunity.
- Maximum screw penetration into chassis mounting holes is 0.125 inches.
- To comply with emissions specifications, all four mounting hole pads must be electrically connected to a common metal chassis. Chassis/Cover option is recommended. Refer to Operating Instructions for additional information.
- Common RF shielding precautions may need to be taken to assure emissions compliance. Refer to Operating Instructions for additional information.
- Power Fail (AC-Good) feature provides a logic-low warning signal from an open collector transistor output 2ms prior to loss of output from AC failure.
- Forced-Air cooling rating of 100W requires an air speed of 200LFM flowing past a point one inch above the main isolation transformer.
- Baseplate cooling rating of 85W requires a one-square-foot 0.09"-thick aluminum area attached to bottom four mounting holes.
- Rated 8A maximum when convection cooled only.
- Rated 1A maximum when convection cooled only.
- Rated 50W maximum output power when convection cooled; 70W when baseplate or forced-air cooled (66W SRW-100-1009).

## MAXIMUM OUTPUT POWER vs. AMBIENT TEMPERATURE



## CONNECTOR SPECIFICATIONS

P1	AC Input (Single)	Terminal block with 4-40 inch screws on 0.325 inch centers with #4 spade terminals.
P1	AC Input (Multiple)	0.156 friction lock header mates with Molex 09-50-3031 or equivalent crimp terminal housing with Molex 08-50-0189 or equivalent crimp terminal.
P2	DC Output (Single)	6-32 screw down terminal mates with #6 ring tongue terminal. (10 in-lb max.)
P2	DC Output (Multiple)	0.156 friction lock header mates with Molex 09-50-3101 or equivalent crimp terminal housing with Molex 08-50-0189 or equivalent crimp terminal.
G	Ground	0.187 quick disconnect terminal.
P3	Option/Sense (Single)	0.100 friction lock header mates with Molex 22-01-2047 or equivalent crimp terminal housing with Molex 6459 or equivalent crimp terminal.
P3	Option (Multiple)	0.100 friction lock header mates with Molex 22-01-2027 or equivalent crimp terminal housing with Molex 6459 or equivalent crimp terminal.