

6

5

4






3

2

1

used for:

D-SUB



POS.	A -0.76	B1 -0.25	B2+0.25	C	D -0.3	PART NO.
15	39.52	24.79	25.12	33.30 +0.15/-0.1	6.12	163C50019X
25	53.42	38.50	38.84	47.04 ±0.13	5.99	163C50029X
37	69.70	54.96	55.30	63.50 ±0.13	5.99	163C50039X

NOTES:

- METALSHELLS: STEEL; min. 315pin TIN OVER 40-80pin NICKEL
- INSULATORS: PBTP GF UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY
PLATING: 30pin HARD GOLD over min. 50min NICKEL
- ADAPTER SCREW: COPPER ALLOY; NICKEL PLATED
- MAXIMUM TORQUE VALUE FOR THREAD: 6in.LB
- CONNECTOR IS PART MARKED: **PART NO. CONEC ABC**

Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance	dim. in mm
2009	date
drawn	27.02.
appd.	27.02.
norm	DIN 41652
d-old	
CONEC	

scale:	2:1 (5:1)
material:	SEE NOTES
title:	
D-SUB ADAPTER	
15-37pos.	
Plug / Socket	
dwg no:	AutoCAD 2006
16K2A897	
part no:	SEE TABLE
DIN-A	3
sh:	1/1

6

5

4

3

2

1