175024-1 ✔ ACTIVE

Positive Lock | Positive Lock 250

TE Internal #: 175024-1

Quick Disconnect Receptacle, Uninsulated, 15 – 10 AWG, 1.65 – 5.26 mm² Wire, 6.35 mm [.25 in] Tab Width, F-Crimp, Straight, Brass, Positive Lock 250

View on TE.com >

Terminals & Splices > Quick Disconnects







Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **1.65 – 5.26 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Electrical Characteristics

Voltage Rating	250 V

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Pre-Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

Downloaded from Arrow.com.

Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	With

Dimensions

Product Length	21.2 mm[.834 in]
Compatible Insulation Diameter Range	3 – 5.1 mm[.118 – .2 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	1.65 – 5.26 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Packaging Features

Packaging Quantity	4000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous

Downloaded from Arrow.com.

materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 2391865-2
250 sleeve PL YELLOW transparent



TE Part # 2376591-2
250 FASTON PCB TAB TPBR



TE Part # 2391865-1
POSITIVE LOCK 250 (6.3 MM) SLEEVE



TE Part # 175022-2
250 POSITIVE REC EX MK-2



TE Part # 2150062-2
OCEAN_2.0_Applicator-E-150F220F-REA



TE Part # 2376579-2
250 FASTON PCB TAB TPBR




TE Part # 2376595-2
250 FASTON PCB TAB TPBR



TE Part # 2232343-2
250 PL EX FLAG REC. 18-12AWG PTBR FLAT



TE Part # 2232343-1
250 PL EX FLAG REC. 18-12AWG PTBR




TE Part # 7-2150062-7
OCEAN_2.0_SPARE_PART_KIT-150F220F



TE Part # 2376582-2
250 FASTON PCB TAB TPBR

Also in the Series | Positive Lock 250



Automotive Terminals(1)



Crimp Terminal Housings(163)



Insertion & Extraction Tools(2)



Insulation Boots & Sleeves(5)

Downloaded from Arrow.com.




Quick Disconnects(162)

Customers Also Bought




TE Part #170325-5
187 PL MKII REC. 20-16AWG PTBR



TE Part #170329-1
250 PL MKII REC. 15-10AWG PTBR



TE Part #175178-1
PL EX 250 REC TERMINAL-FLAG 12-10 PTPB




TE Part #176774-5
FF 250 PLUG HSG 3P NYLON NAT



TE Part #1747066-4
GRACE INERTIA CONN 2.5 PLUG HSG 4P NATUR




TE Part #CAT-G7534A-P729
STD Temp Sig GRACE INERTIA Plug



TE Part #1-1903388-2
GIC 2.5 W PLUG HSG 2P RED



TE Part #1971031-1
Receptacle contact for GIC 2.0



TE Part #2150487-1
OCEAN_2.0_APPLICATOR-E-120F250F-REM

Documents

Product Drawings

250 PL EX REC. 15-10AWG PTBR

Japanese

CAD Files

Customer View Model

ENG_CVM_CVM_175024-1_G2.3d_igs.zip

English

Customer View Model

Downloaded from Arrow.com.

ENG_CVM_CVM_175024-1_G2.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_175024-1_G2.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

Positive Lock Receptacles

English

110_Positive_Lock_Housings

English

POS_LOCK_MII_QRG

English

2P_Positive_Lock_HSGS

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

POSITIVE LOCK EX CONTACT

English

Agency Approvals

Agency Approval Document

English

Downloaded from Arrow.com.