

NAWU Series

Surface Mount Aluminum Electrolytic Capacitors



FEATURES

- CYLINDRICAL V-CHIP CONSTRUCTION FOR SURFACE MOUNTING
- HIGH TEMPERATURE, EXTEND LIFE (5000 HOURS @ 105°C)
- 4X6.3mm ~ 18X22mm CASE SIZES
- DESIGNED FOR REFLOW SOLDERING
- **MEETS THE REQUIREMENTS OF AEC-Q200***


*Contact NIC for supporting test data



CHARACTERISTICS

Rated Voltage Range	6.3 ~ 400Vdc									
Rate Capacitance Range	2.2 ~ 220μF									
Operating Temp. Range	-40°C ~ +105°C									
Capacitance Tolerance	±20% (M)									
Max. Leakage Current After 2 Minutes @ 20°C	0.01CV or 3μA whichever is greater							≤ 1000μF = 0.03CV + 15μA		
								> 1000μF = 0.02CV + 25μA		
Tan δ @120Hz/20°C	W.V. (Vdc)	6.3	10	16	25	35	50	160	200	400
	S.V.(Vdc)	8	13	20	32	44	63	200	250	450
	Tan δ	0.32	0.24	0.20	0.16	0.13	0.12	0.2	0.2	0.25
Low Temperature Stability Impedance Ratio @ 120Hz	W.V. (Vdc)	6.3	10	16	25	35	50	160	200	400
	Z-25°C/Z+20°C	4	3	2	2	2	2	3	3	6
	Z-40°C/Z+20°C	10	7	5	3	3	3	6	6	10
Load Life Test @ 105°C 5,000hrs	Capacitance Change	Within ± 30% of initial measured value								
	Tan δ	Less than 300% of specified max. value								
	Leakage Current	Less than specified max. value								

PART NUMBER SYSTEM



Optional: Suitable for automotive equipment, sourced to special production and inspection at IATF-16949 certified production site.

PEAK REFLOW TEMPERATURE CODES

Code	Peak Reflow Temperature
L	250°C
K	245°C
J	240°C
H	235°C
G	230°C

TERMINATION FINISH & PACKAGING OPTIONS CODES

Code	Finish & Reel Size
LB	Sn-Bi Finish & 15" Reel
LS	100% Sn Finish & 15" Reel

Note: 16mm & 18mm diameter parts are only available with Sn finish

PRECAUTIONS

Please review the notes on correct use, safety and precautions found at <https://www.niccomp.com/wp-content/uploads/files/aluminum/AlumApplInfoCautions.pdf>
If in doubt or uncertainty, please review your specific application - process details with NIC's technical support personnel: tpmg@niccomp.com

NAWU Series

Surface Mount Aluminum Electrolytic Capacitors



STANDARD VALUES, PART NUMBERS AND MAXIMUM RIPPLE CURRENT

Part Number	W.V. (Vdc)	Cap. (μ F)	Dissipation Factor (Tan δ)	Ripple Current Rating (mA @ 105°C/120Hz)	Load Life Hours @ +105°C
NAWU330M6.3V5X6.3LLBF	6.3	33	0.32	35	5,000
NAWU470M6.3V5X6.3LLBF		47	0.32	36	5,000
NAWU101M6.3V6.3X6.3LLBF		100	0.32	60	5,000
NAWU221M6.3V6.3X8LLBF		220	0.32	101	5,000
NAWU220M10V5X6.3LLBF	10	22	0.24	30	5,000
NAWU330M10V5X6.3LLBF		33	0.24	35	5,000
NAWU470M10V6.3X6.3LLBF		47	0.24	50	5,000
NAWU101M10V6.3X8LLBF		100	0.24	81	5,000
NAWU100M16V4X6.3LLBF	16	10	0.20	18	5,000
NAWU220M16V5X6.3LLBF		22	0.20	30	5,000
NAWU330M16V6.3X6.3LLBF		33	0.20	48	5,000
NAWU470M16V6.3X6.3LLBF		47	0.20	50	5,000
NAWU101M16V6.3X8LLBF		100	0.20	81	5,000
NAWU100M25V5X6.3LLBF	25	10	0.16	25	5,000
NAWU220M25V6.3X6.3LLBF		22	0.16	42	5,000
NAWU330M25V6.3X6.3LLBF		33	0.16	48	5,000
NAWU470M25V6.3X8LLBF		47	0.16	63	5,000
NAWU4R7M35V4X6.3LLBF	35	4.7	0.13	15	5,000
NAWU100M35V5X6.3LLBF		10	0.13	25	5,000
NAWU220M35V6.3X6.3LLBF		22	0.13	42	5,000
NAWU330M35V6.3X8LLBF		33	0.13	57	5,000
NAWU2R2M50V4X6.3LLBF	50	2.2	0.12	11	5,000
NAWU3R3M50V4X6.3LLBF		3.3	0.12	14	5,000
NAWU4R7M50V5X6.3LLBF		4.7	0.12	19	5,000
NAWU100M50V6.3X6.3LLBF		10	0.12	30	5,000
NAWU220M50V6.3X8LLBF		22	0.12	49	5,000
NAWU100M160V10X10.8JLBF	160	10	0.20	43	5,000
NAWU220M160V12.5X14HLBF		22	0.20	112	5,000
NAWU330M160V12.5X14HLBF		33	0.20	137	5,000
NAWU470M160V16X17GLSF		47	0.20	180	5,000
NAWU680M160V16X17GLSF		68	0.20	215	5,000
NAWU820M160V16X17GLSF		82	0.20	235	5,000
NAWU101M160V18X17.5GLSF		100	0.20	320	5,000
NAWU121M160V18X22GLSF		120	0.20	340	5,000
NAWU3R3M200V8X10.8JLBF	200	3.3	0.20	31	5,000
NAWU4R7M200V8X10.8JLBF		4.7	0.20	37	5,000
NAWU100M200V10X10.8JLBF		10	0.20	43	5,000
NAWU220M200V12.5X14HLBF		22	0.20	112	5,000
NAWU330M200V12.5X14HLBF		33	0.20	137	5,000
NAWU470M200V16X17GLSF		47	0.20	180	5,000
NAWU680M200V16X17GLSF		68	0.20	215	5,000
NAWU680M200V18X17.5GLSF		68	0.20	270	5,000
NAWU101M200V18X22GLSF		100	0.20	330	5,000
NAWU2R2M400V8X10.8JLBF	400	2.2	0.25	25	5,000
NAWU3R3M400V10X10.8JLBF		3.3	0.25	36	5,000
NAWU4R7M400V10X10.8JLBF		4.7	0.25	38	5,000
NAWU100M400V12.5X14HLBF		10	0.25	57	5,000
NAWU220M400V16X17GLSF		22	0.25	115	5,000
NAWU270M400V18X17.5GLSF		27	0.25	125	5,000
NAWU330M400V18X22GLSF		33	0.25	160	5,000

For Automotive Equipment see part number system

RIPPLE CURRENT

FREQUENCY CORRECTION FACTOR


Frequency Hz	100 ≤ F < 1K	1K ≤ F < 10K	10K ≤ F < 100K	100K ≤ F
C ≤ 4.7	1.00	1.30	1.50	1.80
4.7 < C ≤ 33	1.00	1.20	1.30	1.45
33 < C	1.00	1.10	1.20	1.30
All 160V ~ 400V	50	120	300	1K
	0.75	1.00	1.20	1.30
				10K ≤ F
				1.50

STANDARD PRODUCTS AND CASE SIZE TABLE D x L (mm)

Cap (μF)	Code	Working Voltage (Vdc)								
		6.3	10	16	25	35	50	160	200	400
2.2	2R2	-	-	-	-	-	4X6.3	-	-	8X10.8
3.3	3R3	-	-	-	-	-	4X6.3	-	8X10.8	10X10.8
4.7	4R7	-	-	-	-	4X6.3	5X6.3	-	8X10.8	10X10.8
10	100	-	-	4X6.3	5X6.3	5X6.3	6.3X6.3	10X10.8	10X10.8	12.5X14
22	220	-	5X6.3	5X6.3	6.3X6.3	6.3X6.3	6.3X8	12.5X14	12.5X14	16X17
27	270	-	-	-	-	-	-	-	-	18X17.5
33	330	5X6.3	5X6.3	6.3X6.3	6.3X6.3	6.3X8	-	12.5X14	12.5X14	18X22
47	470	5X6.3	6.3X6.3	6.3X6.3	6.3X8	-	-	16X17	16X17	-
68	680	-	-	-	-	-	-	16X17	16X17	-
82	820	-	-	-	-	-	-	16X17	-	-
100	101	6.3X6.3	6.3X8	6.3X8	-	-	-	18X17.5	18X22	-
120	121	-	-	-	-	-	-	18X22	-	-
220	221	6.3X8	-	-	-	-	-	-	-	-


DIMENSIONS D x L (mm)

Case Size	φD	L max.*	A ± 0.2	B ± 0.2	I ± 0.2	W	P ± 0.2
4x6.3	4.0	6.3	4.3	4.3	1.8	0.5 ~ 0.8	1.0
5x6.3	5.0	6.3	5.3	5.3	2.2	0.5 ~ 0.8	1.4
6.3x6.3	6.3	6.3	6.6	6.6	2.5	0.5 ~ 0.8	2.2
6.3X8	6.3	8.0	6.6	6.6	2.5	0.5 ~ 0.8	2.2
8x10.8	8.0	10.8	8.3	8.3	2.9	0.7 ~ 1.1	3.2
10x10.8	10.0	10.8	10.3	10.3	3.2	1.0 ~ 1.4	4.6
12.5x14	12.5	14	12.8	12.8	4.5	1.0 ~ 1.4	4.6
16x17	16	17	16.3	16.3	5.2	1.7 ~ 2.1	7.0
18x17.5	18	17.5	19.0	19.0	6.5	1.7 ~ 2.1	7.0
18X22	18	*21.5 ^{+0.5} / _{-1.0}	19.0	19.0	6.5	1.7 ~ 2.1	7.0



RECOMMENDED LAND PATTERN (mm)


Case Dia.	a	b	c
4	1.0	2.6	1.8
5	1.4	3.0	1.8
6.3	1.8	3.6	1.8
8	2.8	4.1	2.1
10	4.3	4.4	2.5
12.5	4.3	5.8	2.5
16	6.6	6.5	5.0
18	6.6	7.7	5.0



PEAK REFLOW TEMPERATURE AND DURATION


Voltage	Diameter	Time above 200°C (t)	Time above 217°C (t1)	Time above 230°C (t2)	Peak Temperature 5 seconds (T)
6.3 ~ 50V	4 ~ 6.3mm ϕ	70 sec. max.	60 sec. max.	40 sec. max.	250°C
160 ~ 400V	8 ~ 10mm ϕ	50 sec. max.	30 sec. max.	20 sec. max.	240°C
	12.5mm ϕ	45 sec. max.	20 sec. max.	10 sec. max.	235°C

Capacitors can withstand two times reflow at the above conditions.
Second reflow shall be at least one hour after natural cool to room temperature.



PEAK REFLOW TEMPERATURE AND DURATION

Voltage	Diameter	Time above 200°C (t)	Time above 217°C (t1)	Peak Temperature 5 seconds (T)
160 ~ 400V	16 ~ 18mm ϕ	30 sec. max.	15 sec. max.	230°C




NAWU Series

Surface Mount Aluminum Electrolytic Capacitors



CARRIER TAPE DIMENSIONS (mm)

Case Size	A ±0.5	B ±0.2	C ±0.3	D ±0.1	P ±0.1	T ±0.2	t max.	S ± 0.1
4 x 6.3	4.7	4.7	12.0	5.5	8.0	6.4	0.6	-
5 x 6.3	5.7	5.7	12.0	5.5	12.0	6.4	0.6	-
6.3 x 6.3	7.0	7.0	16.0	7.5	12.0	6.5	0.6	-
6.3 x 8	7.0	7.0	16.0	7.5	12.0	8.2	0.6	-
8 x 10.8	8.7	8.7	24.0	11.5	16.0	11.1	0.6	-
10 x 10.8	10.7	10.7	24.0	11.5	16.0	11.2	0.6	-
12.5 x 14	13.2	13.2	32.0	14.2	24.0	14.3	0.6	28.4
16 x 17	17.5	17.5	44.0	20.2	28.0	17.3	0.6	40.4
18X17.5	19.5	19.5	44.0	20.2	32.0	17.8	0.6	40.4
18X22	19.5	19.5	44.0	20.2	32.0	22.5	0.6	40.4





V-Chip 15" (380mm) Reels (LB suffix)

Dimensions (mm)

Case Size	Tape Width	W1	W2
4x6.3, 5x6.3	12.0	12.5 ~ 14.0	15.5 ~ 20.0
6.3x6.3, 6.3x8	16.0	16.5 ~ 18.0	19.5 ~ 24.0
8x10.8, 10x10.8	24.0	24.5 ~ 26.0	27.5 ~ 32.0
12.5x14	32.0	33.0 ~ 34.0	36.5 ~ 38.5
16x17, 18x17.5, 18x22	44.0	45.0 ~ 46.0	48.5 ~ 50.5

Case Size	Tape Width	A	B	C	D	E
4x6.3, 5x6.3	12.0	φ380 ±2	φ50 min.	φ13 ±0.5	φ21 ±1.0	2.0 ±0.5
6.3x6.3, 6.3x8	16.0					
8x10.8, 10x10.8	24.0					
12.5x14	32.0					
16x17, 18x17.5, 18x22	44.0					



Case Size	Quantity per Reel 15" (380mm)
4x6.3	2000
5x6.3	1000
6.3x6.3	1000
6.3x8	900
8x10.8	500
10x10.8	500
12.5x14	250
16x17	200
18x17.5	175
18x22	125