






PRODUCT #	PCB THICKNES
89092-101LF	1.6 & 2.4



PRODUCT AFTER PC BOARD APPLICATION.



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

NOTES:

- 1 INDICATED HOLES ARE UNPLATED.
- 2 MATERIAL: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
COLOR NATURAL.
- 5 THIS PRODUCT WITH "LF" SUFFIX MEETS EUROPEAN
UNIONDIRECTIVES AND OTHER COUNTRY REGULATIONS AS
DESCRIBED IN GS -22-008.
- 6 THE HOUSING WILL WITHSTAND EXPOSURE TO 260 DEGREE PEAK TEMPERATURE
FOR 20 SECONDS IN WAVE SOLDER APPLICATION WITH A 1.6 MM MINIMUM THICK
CIRCUIT BOARD.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		ELECTRONICS	
SEE NOTE 2									
ltr	ecr	no	dr	date	linear	projection	title		
A	H40355	DOB	940616				RA FEMALE HSG		
B	H50047	RVI	950119				HYBRID 12MM PRESS PEG		
C	H90478	DOB	990816		angles		product family		
D	p005-0383	Clu	051011	dr	H.Bouwknegt	931206	size		
E	p005-0406	Clu	051027	eng	D.Andrews	931206	dwg no		
				chr	D.Andrews	950119	scale		
				app	H.Coolijmans	950119	5:1		
sheet	revision			E			A2	89092	code
index	sheet			1					213
									sheet
									1 of 1

PDM: Rev.E

STATUS: Released

Printed: May 19, 2011