


 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



 Active

Always EU RoHS/ELV Compliant (Statement of Compliance)

? Splice
? Not Sealed
? Splice Type = Butt
? Butt Splice Type = Standard
? Body Style = PLASTI -GRIP

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

? [JAPANESE](#) (PDF, English)

Catalog Pages/Data Sheets:

? None Available

Product Specifications:

[PLASTI-GRIP TERMINALS AND SPLICES WITH INSULATION SL...
\(PDF, English\)](#)

Application Specifications:

? None Available

Instruction Sheets:

? None Available

CAD Files:

? None Available

List all Documents

Additional Information:

? Product Line Information

Related Products:

? Tooling

(Please use the Product Drawing for all design activity)

Product Type Features:

? Product Type = Splice
 ? Sealed = No
 ? Splice Type = Butt
 ? Body Style = PLASTI -GRIP
 ? Insulation = Yes
 ? Insulation Support = Insulation Support
 ? Insulation Diameter (mm [in]) = 5.80 [.228]
 Max.
 ? Material = Copper
 ? Finish = Tin
 ? Color = Yellow
 ? Comment = When using two or more wires in
 either end of a splice the combined cross
 sectional area must be within the wire size
 range listed.

Body Related Features:

? Butt Splice Type = Standard
 ? Wire Range (mm [AWG]) = 3.00 - 6.00 ² [12-10]
 ? Wire Range (CMA) = 5,180 - 13,100

Industry Standards:

- ? Government/Industry Qualification = No
- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

? Packaging Method = Loose Piece

Other:

? Brand = AMP