









PRODUCT NUMBER	PITCH
TSxx51xC00J0G	5.08 mm



Material

- ItemⒶ Clamp: Brass(CuZn), Ni plating
- ItemⒷ Terminal screw: Steel Zinc plating "-" slot type
- ItemⒸ Female contact: PhBz, Tin plated
- ItemⒹ Top body: Thermoplastic (UL94V-0)
- ItemⒺ Bottom body: Thermoplastic (UL94V-0)
- ItemⒻ With flange screw: Steel Zinc plating M2.5 "+/-" combination type

Electrical cULus/VDE/TUV



- Voltage rating: 300VAC/300VAC/300VAC
- Current rating: 15A/17A/15A
- Wire range: 2.5mm²/0.34-2.5mm²
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 3.5Lb-In./0.5Nm/0.4Nm
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety approval:   

N = Number of poles
 Dim A=Nx5.08+0.5
 Dim B=(N-1)x5.08
 Dim C=(N-1)x5.08
 Dim D=(N-1)x5.08+10.16
 Dim E=(N-1)x5.08+15.24
 Dim F=Nx5.08

poles	Tolerance
2-6p	±0.15
7-12p	±0.25
13-18p	±0.30
19-24p	±0.40

PART NO.: TS xx 51 x C 00J0 G

Solid block	No. of poles	Color	RoHS compliant (lead<4%) In copper Alloy
02	2 poles	0 Black (RAL9005)	
03	3 poles	2 Red (RAL3001/D)	
...	...	3 Orange(RAL2011/P)	
24	24 poles	4 Yellow(RAL1018/A)	
		5 Green(RAL6018/T)	
		6 Blue (RAL5015/A)	
		8 Grey(RAL7035/D)	
		9 White(RAL1102)	
		C Green(RAL6018/U)	

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection 	product family TERMINAL BLOCK
ltr	ecn	no	dr	date	tolerances unless otherwise specified	MM	title TERMINAL BLOCK
					angles X±0.5		PLUGGABLE PLUG,HOOK ON ENTRY SIDE,WITH FLANGE
					parallel X.X±0.3		dwg no TSxx51xC00J0G
					perpendicular X.XX±0.1	scale	sheet 1 of 1 size A4
					dr EVIN ZHONG 041914		CUSTOMER Drawing
					enrg EVIN ZHONG 041914		
					chr HANKE FENG 041914		
					appd SHI JUN 041914		
sheet index	revision sheet	A	1				