



REVISIONS			
SYM	ZONE	ECN, ERN NO.	DATE
A		PROPOSAL	MAY04/06
			L.CHAN



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

AMPHENOL PART NO: RJEO3-166-0X20

- 1 = 06 μ" GOLD
- 2 = 15 μ" GOLD
- 3 = 30 μ" GOLD
- 4 = 50 μ" GOLD

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

MATERIALS:
PLASTIC HOUSING: ENGINEERING THERMOPLASTIC
FLAMMABILITY RATING UL94V-0

CONTACTS:
PHOSPHOR BRONZE
PLATING: REFER TO PART NUMBER FOR GOLD
THICKNESS ON MATING SURFACES.
50 μ" [1.27 MICRONS]
MIN. NICKEL UNDERPLATE.
100 μ" [2.54 MICRONS]
MIN. MATTE-TIN OR GOLD FLASH
ON CONTACT TAILS.

RECOMMENDED SOLDERING TEMPERATURE:
WAVE SOLDERING AT 240°C MAXIMUM FOR
5 SEC MAXIMUM

DRAWN	PAULW	DATE	MAY04/06
DESIGNED			
CHECKED	CHIGOW		MAY04/06
I. E. APPRD.			
Q. A. APPRD.			
DWG. APPRD.			
ENG. REL. NO.			
REF.			
DIMENSIONS ARE IN INCHES [mm]	CODE	ID. NO.	03554
SCALE	4/1	WT.	-----
SURF.	-----	SHEET	1 of 1

Amphenol Canada Corp.

TITLE MODULAR JACK 6 POSITION,
6 CONTACTS (WITH SIDE FLANGES)
— RoHS COMPLIANT

DWG	DRAWING NO.	REV.
C	P-RJEO3-166-0X20	A