234A011-100-0 ✔ ACTIVE


RAYCHEM

TE Internal #: 136852-000

Right Angle Heat Shrink Boot, 100 Material Code, 100 Material Systems Code, Adhesive Purchased Separately, -30 – 105 °C [-22 – 221 °F]

View on TE.com >

Wire Protection & Management > Heat Shrink Shapes > Heat Shrink Boots



Body Orientation: **Right Angle**

Material Code: **100**

Material Systems Code: **100**

Adhesive Requirement: **Adhesive Purchased Separately**

Operating Temperature Range: **-30 – 105 °C [-22 – 221 °F]**

Features

Configuration Features

Adhesive Requirement	Adhesive Purchased Separately

Body Features

Primary Product Material	Semi-flexible ZEROHAL Polyolefin
Material Code	100
Material Systems Code	100

Housing Features

Body Orientation	Right Angle

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Other

Adhesive Code	S1006, S1030, S1048, S1125

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold

Downloaded from Arrow.com.

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 9-120035-6
HarnWare/HarnVis Renewal Charge



TE Part # 9-120035-5
HarnWare/HarnVis Purchase Charge


Customers Also Bought



TE Part #139692-000
214A011-100-0



TE Part #ZPF000000000140615
983-3KE-D 10



TE Part #856942-000
234A021-100-0




TE Part #02560396-006
LVDT HR 2000 MC ASSY


Downloaded from Arrow.com.




TE Part #3822543004
44A1121-22-0/9-9



TE Part #530721-3
MINI-BOX EXT KEY KIT




TE Part #530721-4
MINI-BOX EXT KEY KIT



TE Part #1-530743-7
MINI BOX PIN HDR ASY 70 PS RA



TE Part #1-530745-7
MINI-BOX RCPT ASSY 70P SEALED



TE Part #769537-000
214A032-100-0

Documents

Product Drawings

234A011-100-0

English

Datasheets & Catalog Pages

1654025_Sec4_-100

English

Raychem Molded Parts Visual Guide

English

Product Specifications

Product Specification

English

Downloaded from Arrow.com.