


PCB layout, mounting side (thickness 1,6 mm)



0955 166 6812 333	2	4-40 UNC	Black insulator	Samples
0955 166 3812 741	1	4-40 UNC	Black insulator	Reel Packaging (140 connectors)
0955 166 6812 741	2			
0955 166 7812 741	3			
0955 166 3811 741	1	M3		
0955 166 6811 741	2			
0955 166 7811 741	3			
Part number	PL	Thread		

Max. Temperature: 260°C during 10 seconds
Find further technical information on DS 09550200301

		All Dimensions in mm Original Size DIN A3		Scale 2:1		Free size tol.		Ref.	
All rights reserved		Created by ZHUANGJ		Inspected by LUOK		Standardisation HOFFMANN		Date 2018-10-17	
Department EL PD		Title D-Sub angled STD 9-pole male with screw nut		State Final Release		Doc-Key / ECM-Nr. 100518042/UGD/001/C 500000141378			
HARTING Electronics GmbH D-32339 Espelkamp		Type TB		Number 0955166X81X		Rev. C		Page 1/1	