



Part Number : [1200878784](#)

Product Description : Micro-Change (M12) to Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 3 Poles, Female (Straight) to Male (Straight), 24 AWG, WSOR Cable, 3.0m (9.84') Length

Series Number : 120087

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 483030B41M030

Documents and Resources

Drawings

[1200878784_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120087
Description	Micro-Change (M12) to Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 3 Poles, Female (Straight) to Male (Straight), 24 AWG, WSOR Cable, 3.0m (9.84') Length
IP Rating	IP67
Product Name	Micro-Change (M12), Nano-Change (M8)
Type	Double Ended
UPC	889056132497

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC/DC

Physical

Cable Diameter	4.50mm (.177")
Cable Length	3.0m (9.84')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Nano-Change (M8)
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPU

Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	WSOR
Wire Size (AWG)	24

This document was generated on Jun 06, 2026