








VIEW A



NOTE

1. MATERIAL : PC/PET (UL94 V-0)
2. MATED HOUSING : 35180-040*
35180-060*
3. APPLICABLE TERMINAL : 35745-0*10
4. APPLICABLE T.P.A : 104081-028*
5. PRODUCT SPECIFICATION : PS-35180-002
6. FLASH HEIGHT : 0.2mm MAX.



<TABLE>

PART NO.	COLOR
35965-9230	NATURAL
35965-9232	RED
35965-9233	YELLOW
35965-9234	BLUE

NEW RELEASE EC NO: KOR2011-0009 DRWN:HTSONG CHKD:SHCHU APPR:YUNS IKK IM	2010/08/05 2010/08/05 2010/08/06	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 3:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
					mm	INCH	DRAWN BY HTSONG	DATE 2010/02/12	TITLE .070 MULTI FEMALE HOUSING 2P(D TYPE)		
				4 PLACES	± ---	± ---	CHECKED BY SHCHU	DATE 2010/02/12			
				3 PLACES	± ---	± ---	APPROVED BY YSKIM	DATE 2010/02/12			
				2 PLACES	± ---	± ---	MATERIAL NO. SEE TABLE				DOCUMENT NO. SD-35965-923*
				1 PLACE	± 0.30	± ---					
				ANGULAR ± 1 °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION