


PUSH TO OPERATE-RETURNS AUTOMATICALLY TO POSITION SHOWN. PULL TO OPERATE-REMAINS IN OPERATED POSITION UNTIL NEXT FULL STROKE OF PLUNGER




NOTES

- 1 - UNIT INCLUDES CATA LOG LISTING 411SM1-H58
 - 2 - NOTCH IN ACTUATOR PLUNGER WILL PERMIT .045 MAX DISPLACEMENT BETWEEN END OF PLUNGER AND HOLE IN BRACKET
- 3 PLATED TERMINALS WILL ACCEPT "AMP INC" Ø .058 PIN RECEPTACLES

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA			SCALE FULL	DO NOT SCALE PRINT
TOTAL TRAVEL .156 APPROX PUSH DIRECTION .156 APPROX PULL DIRECTION FULL OVERTRAVEL FORCE - 2 LB APPROX	CONTACT ARRANGEMENT S P D T			UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
	30 VOLTS DC RATING			ONE PLACE (.0)	±.030
	SEA LEVEL			TWO PLACE (.00)	±.015
	INDUCTIVE	3 AMP		THREE PLACE (.000)	±.005
	RESISTIVE	5 AMP		ANGLES	±
				WEIGHT	.02 LB APPROX

RASTER

DRAWN

CSL 9 MAR 01

SAV 9 MAR 01

CHECK

REVISIONS

CHECK

ISSUE

M

PAGE 1 OF 1

17AC28-H58

RELEASE NO. PR-2681

REPLACES