

Honeywell Sensing and Control

Search



narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6158)
- Switches (9781)
- Wireless (45)

Technology

- Control and Instrumentation (890)
- Electromechanical (9303)
- Magnetic (538)
- Platinum thin film (56)
- Thick Film (1372)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



[Wireless Web Site WGLA and WPMM XYR6000™](#)

[find out more](#)

white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

Need help?

[Click here to contact us](#)

SSCMRNN001PG2A3

(Home : [Products](#) : [Sensors](#) » [Silicon Pressure Sensors](#) » [Low Pressure Sensors](#) » [TruStability® SSC](#))



Actual product appearance may vary.

TruStability® SSC Series-Standard Accuracy, ±2% total error band, digital I²C address: 0x28, SMT, RN: single radial barbed port, gage, 0 psi to 1 psi, 3.3 Vdc, dry gases only, no special options

[Sales & Service](#) [Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Measurement Type	Gage
Signal Conditioning	Amplified
Pressure Range	0 psi to 1 psi
Overpressure	10 psi
Supply Voltage	3.3 Vdc
Supply Current	1.6 mA typ.
Temperature Compensation	Yes
Output Calibration	Yes
Response Time	1 ms max.
Port Style	RN: single radial barbed port
Package Type	SMT
Accuracy (Best Fit Straight Line)	±0.25%
Shock	MIL-STD-202F, Method 213B, Condition F
Vibration	MIL-STD-202F, Curve AK (20.7 g random)
Operating Temperature	-40 °C to 85 °C [-40 °F to 185 °F]
Compensated Temperature Range	-20 °C to 85 °C [-4 °F to 185 °F]
Storage Temperature	-40 °C to 85 °C [-40 °F to 185 °F]
Media Compatibility	Dry gases only
Comment	No special options
Availability	Global
Series Name	TruStability® SSC

contacts

- Customer Service
- Technical Support
- Global Sales & Service
- View Site Demo
- Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

my links

- [Login to iCOM](#)
- [Login to Rep/AD Portal](#)
- [Login to Digital University](#)

News Center

HONEYWELL INTRODUCES TRUSTABILITY® NSC SERIES, UNCOMPENSATED / UNAMPLIFIED BOARD MOUNT PRESSURE SENSORS

HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER

HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

MICRO SWITCH Anniversary site