






	1	2	3	4	5	6	7																																										
A						NOTE: Voltage Rating: 100V AC/DC Current Rating: 1A AC/DC Withstanding Voltage: 500V AC/minute Insulation Resistance: 500MΩ Min Temperature Range: -40°C to +105°C		A																																									
B						Contact Material: Brass Contact Plating: Tin over Nickel ① Insulator: Nylon 6T, UL94V-0, Beige; Mating with A-WBP-G001EG-xxCB01 Series Housing		B																																									
C						Order Code: A-WBP-G001EA-xxSR01 Pin Count		C																																									
D						<table><thead><tr><th rowspan="2">PART NO.</th><th colspan="2">Dimensions</th></tr><tr><th>A</th><th>B</th></tr></thead><tbody><tr><td>A-WBP-G001EA-02SR01</td><td>1.50</td><td>6.00</td></tr><tr><td>A-WBP-G001EA-03SR01</td><td>3.00</td><td>7.50</td></tr><tr><td>A-WBP-G001EA-04SR01</td><td>4.50</td><td>9.00</td></tr><tr><td>A-WBP-G001EA-05SR01</td><td>6.00</td><td>10.50</td></tr><tr><td>A-WBP-G001EA-06SR01</td><td>7.50</td><td>12.00</td></tr><tr><td>A-WBP-G001EA-07SR01</td><td>9.00</td><td>13.50</td></tr><tr><td>A-WBP-G001EA-08SR01</td><td>10.50</td><td>15.00</td></tr><tr><td>A-WBP-G001EA-09SR01</td><td>12.00</td><td>16.50</td></tr><tr><td>A-WBP-G001EA-10SR01</td><td>13.50</td><td>18.00</td></tr><tr><td>A-WBP-G001EA-11SR01</td><td>15.00</td><td>19.50</td></tr><tr><td>A-WBP-G001EA-12SR01</td><td>16.50</td><td>21.00</td></tr><tr><td>A-WBP-G001EA-13SR01</td><td>18.00</td><td>22.50</td></tr></tbody></table>		PART NO.	Dimensions		A	B	A-WBP-G001EA-02SR01	1.50	6.00	A-WBP-G001EA-03SR01	3.00	7.50	A-WBP-G001EA-04SR01	4.50	9.00	A-WBP-G001EA-05SR01	6.00	10.50	A-WBP-G001EA-06SR01	7.50	12.00	A-WBP-G001EA-07SR01	9.00	13.50	A-WBP-G001EA-08SR01	10.50	15.00	A-WBP-G001EA-09SR01	12.00	16.50	A-WBP-G001EA-10SR01	13.50	18.00	A-WBP-G001EA-11SR01	15.00	19.50	A-WBP-G001EA-12SR01	16.50	21.00	A-WBP-G001EA-13SR01	18.00	22.50	D
PART NO.	Dimensions																																																
	A	B																																															
A-WBP-G001EA-02SR01	1.50	6.00																																															
A-WBP-G001EA-03SR01	3.00	7.50																																															
A-WBP-G001EA-04SR01	4.50	9.00																																															
A-WBP-G001EA-05SR01	6.00	10.50																																															
A-WBP-G001EA-06SR01	7.50	12.00																																															
A-WBP-G001EA-07SR01	9.00	13.50																																															
A-WBP-G001EA-08SR01	10.50	15.00																																															
A-WBP-G001EA-09SR01	12.00	16.50																																															
A-WBP-G001EA-10SR01	13.50	18.00																																															
A-WBP-G001EA-11SR01	15.00	19.50																																															
A-WBP-G001EA-12SR01	16.50	21.00																																															
A-WBP-G001EA-13SR01	18.00	22.50																																															
E								E																																									
F								F																																									
G	RoHS compliant Unit:mm		Scale	Free				Date	Name	Description: Wire to Board Connector Wafer / 90° / SMT / 1.50mm	G																																						
TOLERANCE							Drawn	25.03.2021	Luca																																								
.X			±0.25					Approved	23.05.2022	Segal	ASSMANN WSW-No. A-WBP-G001EA-xxSR01																																						
.XX			±0.20																																														
.XXX			±0.15																																														
H	DIM	TOL	①	Update	23.05.2022	Segal			Drawing-No.	ASS 8883 CO	rev01	H																																					
			②	Drawn	25.03.2021	Luca			Customer-No.				SHEET 2 / 6																																				
	Angle	TOL	Id.	Modification	Date	Name																																											
	1	2	3	4	5	6	7	SV5053																																									

	1	2	3	4	5	6	7																																													
A	Circuit 1   P.C.B LAYOUT							A																																												
B	NOTE: Voltage Rating: 100V AC/DC Current Rating: 1A AC/DC Withstanding Voltage: 500V AC/minute Insulation Resistance: 500MΩ Min Temperature Range: -40°C to +105°C Contact Material: Brass Contact Plating: Tin over Nickel ① Insulator: Nylon 66, UL94V-0, Beige; Mating with A-WBH-G001EG-xxCB01 Series Housing							B																																												
C	Order Code: A-WBP-G001EG-xxTB01							C																																												
D								D																																												
E	<table><tr><th rowspan="2">PART NO.</th><th colspan="2">Dimensions</th></tr><tr><th>A</th><th>B</th></tr><tr><td>A-WBP-G001EG-02TB01</td><td>1.50</td><td>4.50</td></tr><tr><td>A-WBP-G001EG-03TB01</td><td>3.00</td><td>6.00</td></tr><tr><td>A-WBP-G001EG-04TB01</td><td>4.50</td><td>7.50</td></tr><tr><td>A-WBP-G001EG-05TB01</td><td>6.00</td><td>9.00</td></tr><tr><td>A-WBP-G001EG-06TB01</td><td>7.50</td><td>10.50</td></tr><tr><td>A-WBP-G001EG-07TB01</td><td>9.00</td><td>12.00</td></tr><tr><td>A-WBP-G001EG-08TB01</td><td>10.50</td><td>13.50</td></tr><tr><td>A-WBP-G001EG-09TB01</td><td>12.00</td><td>15.00</td></tr><tr><td>A-WBP-G001EG-10TB01</td><td>13.50</td><td>16.50</td></tr><tr><td>A-WBP-G001EG-11TB01</td><td>15.00</td><td>18.00</td></tr><tr><td>A-WBP-G001EG-12TB01</td><td>16.50</td><td>19.50</td></tr><tr><td>A-WBP-G001EG-13TB01</td><td>18.00</td><td>21.00</td></tr><tr><td>A-WBP-G001EG-15TB01</td><td>21.00</td><td>24.00</td></tr></table>							PART NO.	Dimensions		A	B	A-WBP-G001EG-02TB01	1.50	4.50	A-WBP-G001EG-03TB01	3.00	6.00	A-WBP-G001EG-04TB01	4.50	7.50	A-WBP-G001EG-05TB01	6.00	9.00	A-WBP-G001EG-06TB01	7.50	10.50	A-WBP-G001EG-07TB01	9.00	12.00	A-WBP-G001EG-08TB01	10.50	13.50	A-WBP-G001EG-09TB01	12.00	15.00	A-WBP-G001EG-10TB01	13.50	16.50	A-WBP-G001EG-11TB01	15.00	18.00	A-WBP-G001EG-12TB01	16.50	19.50	A-WBP-G001EG-13TB01	18.00	21.00	A-WBP-G001EG-15TB01	21.00	24.00	E
PART NO.	Dimensions																																																			
	A	B																																																		
A-WBP-G001EG-02TB01	1.50	4.50																																																		
A-WBP-G001EG-03TB01	3.00	6.00																																																		
A-WBP-G001EG-04TB01	4.50	7.50																																																		
A-WBP-G001EG-05TB01	6.00	9.00																																																		
A-WBP-G001EG-06TB01	7.50	10.50																																																		
A-WBP-G001EG-07TB01	9.00	12.00																																																		
A-WBP-G001EG-08TB01	10.50	13.50																																																		
A-WBP-G001EG-09TB01	12.00	15.00																																																		
A-WBP-G001EG-10TB01	13.50	16.50																																																		
A-WBP-G001EG-11TB01	15.00	18.00																																																		
A-WBP-G001EG-12TB01	16.50	19.50																																																		
A-WBP-G001EG-13TB01	18.00	21.00																																																		
A-WBP-G001EG-15TB01	21.00	24.00																																																		
F								F																																												
G	RoHS compliant Unit:mm		Scale	Free				Date	Name	Description: Wire to Board Connector																																										
TOLERANCE							Drawn	25.03.2021	Luca	Wafer / 180° / THT / 1.50mm																																										
.X			±0.25					Approved	23.05.2022	Segal	ASSMANN WSW-No.																																									
.XX			±0.20								A-WBP-G001EG-xxTB01																																									
.XXX			±0.15																																																	
DIM			TOL	①	Update	23.05.2022	Segal			Drawing-No.		ASS 8883 CO	rev01																																							
		②	Drawn	25.03.2021	Luca	Customer-No.																																														
Angle	TOL	Id.	Modification	Date	Name					SHEET		3 / 6																																								
	1	2	3	4	5	6	7																																													

Downloaded from [Arrow.com](https://arrow.com)

SV5053

