


[All Categories](#) > [EMI Solutions](#) > [EMI Shielding & Gaskets](#) > [Fingerstock and Spring Contacts](#) > [Fingerstock, Gaskets & Metal Grounding Products](#) > [Fingerstock Gaskets and Metal Grounding Products](#) > [Gasket](#) > [Strip Metal Gaskets](#) > [UltraFlex Hollow Core Round Copper Knitted Wire Shielding](#) > [UltraFlex D with PSA Copper Knitted Wire Shielding](#) > [UltraFlex Hollow Core Double Round Copper Knitted Wire Shielding](#) > [Electromesh Tape EMI shielding](#) > [All Mesh Rectangular Strip EMI Gasketing](#) > [All Mesh Round Strip EMI Gasketing](#) > [ElectroMet Impregnated Woven Wire and Expanded Metal Gaskets EMI Shielding Solution](#) > [Ultrasoft Knit EMI Gaskets](#) > Item # 8417-3058-62

Item # 8417-3058-62, Ultrasoft Knit EMI Gaskets

Laird Technologies UltraSoft Knit EMI gasket material consists of a metalized nylon yarn knit over a flame retardant UL 94 HF -1 low density foam polyester core material. The close -knit stitch of the metalized nylon provides a highly effective EMI shield, as well as a smooth, soft surface that will not abrade plated plastic interfaces.



[larger image](#)



[larger image](#)

Specifications

Dimension A	1.000 inches
Dimension A	25.4 mm
Dimension B	1.000 inches
Dimension B	25.4 mm
Dimension C	0.400 inches
Dimension C	10.2 mm
Dimension D	0.586 inches
Dimension D	14.9 mm
Length	7 ft.
Length	2.1 M
EMI Shield Material	Silver plated nylon
Foam Core Material	Low density UL 94 HF -1approved polyester
Pressure Sensitive Adhesive Material	Acrylic