




CONN OUTER MOLD: WM-020

CONN OUTER MOLD: WM-020



Electronic Test:

- 1.100% Test,(Open,Short,Miss Wire)
- 2.Contact Resistance:2 ohm max.
- 3.Insulation Resistance:10M ohm min.
- 4.Hi-Pot:100V DC/10ms



⑦	TIE	1	BLACK L=80mm
⑥	TUBE	2	HEAT SHRINK TUBE BLACK OD1.5*L15mm.
⑤	PE BAG	1/10	CLEAR SIZE:280*330*0.05mm PRINT BLACK"MADE IN CHINA"+ "10PCS"
④	PE BAG	1	CLEAR SIZE:130*230*0.05mm PRINT BLACK"MADE IN CHINA".
③	OUT JACKET	5.5g	OUTER MODEL PVC 45P COLOR BLACK
②	CONN	2	3.5ST MALE Tray6.0mm L=30mm MOLD TYPE NI-PLATED INSULATOR COLOR:BLACK
①	CABLE	1	NOUL 28AWG(7/0.12 TC)*2C(RED,WHITE)+S(43/0.12 TC) JACKET BLACK OD:3.0MM
NO.	NAME	Q'TY	SPECIFICATION

CNC Tech, LLC			
Industrial Cable and Connector Technology			
DRAWN BY	LICHENG	DARWIN, N.D.	
CHECKED BY		CUSTOMER	
APPROVAL BY		ITEM NO.	770-10040-00150
DECIDE BY		DATE	2012-12-17
VERSIONS/EDITION	A/0	PROJECTION	